




**Part Number :** [734205201](#)

**Product Description :** SMP-MAX Plug, Straight,  
Smooth Bore, Panel Mount, Thread-In, Tray, 50 Ohms

**Series Number :** 73420

**Status :** Active

**Product Category :** RF / Coaxial Connectors



---

## Documents and Resources

### Drawings

[734205201\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |                                                                                                         |
|--------------------|---------------------------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                                            |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant                                                                                            |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                                                                          |
| REACH SVHC         | Contains Lead per D(2023)3788-DC (14 Jun 2023)                                                          |
| EU RoHS            | Compliant with Exemption 6(c) per EU 2015/863                                                           |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

Part Details

General

|              |                                                                            |
|--------------|----------------------------------------------------------------------------|
| Status       | Active                                                                     |
| Category     | RF / Coaxial Connectors                                                    |
| Series       | 73420                                                                      |
| Description  | SMP-MAX Plug, Straight, Smooth Bore, Panel Mount, Thread-In, Tray, 50 Ohms |
| Application  | Telecommunications/Networking, RF                                          |
| Product Name | SMP-MAX                                                                    |
| Style        | Panel                                                                      |
| Type         | Subminiature                                                               |
| UPC          | 884982963139                                                               |

Electrical

|                 |                             |
|-----------------|-----------------------------|
| Frequency       | 10 GHz                      |
| Impedance       | 50Ω                         |
| Power / Voltage | VOLTAGE: 330 Vrms@Sea Level |

Physical

|                             |            |
|-----------------------------|------------|
| Cable Attachment            | N/A        |
| Gender                      | Plug       |
| Keying to Mating Part       | N/A        |
| Net Weight                  | 1.711/g    |
| Orientation                 | Straight   |
| Packaging Type              | Tray       |
| Panel Mount                 | Yes        |
| Panel Mount Method          | Thread-In  |
| PCB Mounting                | Round Post |
| PCB Thickness - Recommended | N/A        |
| Reverse Polar               | No         |
| Wire/Cable Type             | N/A        |

**Solder Process Data**

|                              |     |
|------------------------------|-----|
| Lead-Free Process Capability | N/A |
|------------------------------|-----|

---

This document was generated on Feb 26, 2026