



Part Number : [762790416](#)

Product Description : Impact 4 Pair Protective Header Cover for Vertical Header Module, 16 Column

Series Number : 76279

Status : Active

Product Category : Backplane Connectors



Documents and Resources

Drawings

[762790416_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[AS-76060-990-001.pdf](#)

[AS-76060-9997-001.pdf](#)

[PS-45499-002-001.pdf](#)

[PS-75710-999-001.pdf](#)

[PS-76060-999-001.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

[Compliance Statements](#)

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Backplane Connectors
Series	76279
Description	Impact 4 Pair Protective Header Cover for Vertical Header Module, 16 Column
Application	Conventional, Coplanar
Component Type	Cover
Product Name	Impact
UPC	883906573584

Electrical

Current - Maximum per Contact	N/A
Data Rate	N/A
Shielded	No
Shield Type	N/A
Voltage - Maximum	N/A

Physical

Circuits (Loaded)	0
Circuits (maximum)	0
Color - Resin	Natural

Durability (mating cycles max)	N/A
Guide to Mating Part	Yes
Keying to Mating Part	None
Material - Metal	N/A
Material - Plating Mating	N/A
Material - Resin	Polyester
Net Weight	4.091/g
Number of Columns	16
Number of Pairs	4
Number of Rows	12
Orientation	N/A
Packaging Type	Bag
PCB Locator	No
PCB Retention	N/A
PCB Thickness - Recommended	N/A
PC Tail Length	N/A
Pitch - Mating Interface	N/A
Pitch - Termination Interface	N/A
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
Impact 100 Ohm 4 Pair Vertical Backplane Headers	<u>76155</u>
Impact 100 Ohm 4 Pair RAM Right-Angle Headers	<u>76500</u>