

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0934443107

Status:

Active

Overview:

ML-XT Sealed Connection System

Description:

ML-XT Sealed 4 Circuit Receptacle Housing, Pre-Assembled with Small Rear Seal and Cover, Brown

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification 934430010-P (PDF)

Application Specification 934430010-A (PDF)

Packaging Specification 934430002-K (PDF)

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

Agency Certification

UL

E29179

Application tooling part link

Application Tooling Part Link

63824-5300

General

Product Family

Series

Application

Overview

Product Literature Order No

Product Name

UPC

Crimp Housings

93444

Power, Signal, Wire-to-Wire

ML-XT Sealed Connection System

987651-0201

ML-XT

889056258920

Physical

Circuits (maximum)

Color - Resin

Gender

Glow-Wire Capable

Keying to Mating Part

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Polarized to Mating Part

Temperature Range - Operating

4

Brown

Receptacle

No

None

Yes

Nylon

7.820/g

2

Bag

No

N/A

Yes

-55° to +125°C

Electrical

Current - Maximum per Contact

13.0A

Material Info

Reference - Drawing Numbers

Application Specification

Packaging Specification

Product Specification

Sales Drawing

934430010-A

934430002-K

934430010-P

934430030-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

93444 Series

Mates With

ML-XT Sealed 4 Circuit Plug Housing

934453107

Use With

ML-XT Male (Pin) Terminal [845240004](#) (Nickel), ML-XT Male (Pin) Terminal [845240014](#) (Selective Gold), ML-XT 4 Circuit Receptacle Wedgelock [93447](#) , ML-XT Blind Cavity Plug [934941000](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool for ML-XT Sealed

638245300

This document was generated on 11/05/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION