

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0934452108

Status:

Active

Overview:

ML-XT Sealed Connection System

Description:

ML-XT Sealed 3 Circuit Plug Housing, Pre-Assembled with Small Rear Seal and Cover, Orange

Documents:

3D Model	Application Specification 934430010-A (PDF)
Drawing (PDF)	Packaging Specification 934430002-K (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 934430010-P (PDF)	Product Literature (PDF)

Agency Certification

UL	E29179
----	--------

Application tooling part link

Application Tooling Part Link	63824-5300
-------------------------------	------------

General

Product Family	Crimp Housings
Series	93445
Application	Power, Signal, Wire-to-Wire
Overview	ML-XT Sealed Connection System
Product Literature Order No	987651-0201
Product Name	ML-XT
UPC	889056314923

Physical

Circuits (maximum)	3
Color - Resin	Orange
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	6.070/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Temperature Range - Operating	-55° to +125°C

Electrical

Current - Maximum per Contact	13.0A
-------------------------------	-------

Material Info

Reference - Drawing Numbers

Application Specification	934430010-A
Packaging Specification	934430002-K
Product Specification	934430010-P
Sales Drawing	934430020-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[93445](#) Series

Mates With

[ML-XT Sealed 3 Circuit Receptacle Housing 934442108](#)

Use With

[ML-XT Female \(Socket\) Terminal 845250009](#) (Nickel), [ML-XT Female \(Socket\) Terminal 845250032](#) (Selective Gold), [ML-XT 3 Circuit Plug Wedgelock 93448](#) , [ML-XT Blind Cavity Plug 934941000](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool for ML-XT Sealed	638245300

This document was generated on 11/05/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION