



**Part Number :** [936010057](#)  
**Product Description :** Heavy-Duty Turned Crimp Contact for 10A Inserts and Modules, Male, Silver (Ag) Plated Copper Alloy, 1.00mm<sup>2</sup> (18 AWG), 100 per Bag  
**Series Number :** 93601  
**Status :** Active  
**Product Category :** Heavy-Duty Contacts  
**Engineering Part Number :** 7100.4214.0



## Documents & Resources

**Drawings**  
[936010057 sd.pdf](#)

## Product Environment Compliance

### Compliance

|                    |                                                                                                              |
|--------------------|--------------------------------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                                                 |
| China RoHS         | <br>per SJ/T 11365-2006 |
| EU ELV             | Not Relevant                                                                                                 |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                                                                               |
| REACH SVHC         | Not Contained per D(2025)4165-DC (25 June 2025)                                                              |
| EU RoHS            | Compliant with Exemption 6(c) per EU 2015/863                                                                |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

## UKCA - Declaration of Conformity

## CE - Declaration of Conformity

---

## Part Details

### General

|              |                                                                                                                                               |
|--------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| Status       | Active                                                                                                                                        |
| Category     | Contacts                                                                                                                                      |
| Series       | 93601                                                                                                                                         |
| Description  | Heavy-Duty Turned Crimp Contact for 10A Inserts and Modules, Male, Silver (Ag) Plated Copper Alloy, 1.00mm <sup>2</sup> (18 AWG), 100 per Bag |
| Contact Type | Turned Crimp                                                                                                                                  |
| Product Name | Heavy-Duty Connectors                                                                                                                         |
| UPC          | 887191867557                                                                                                                                  |

### Agency

|     |         |
|-----|---------|
| CSA | 256883  |
| UL  | E249674 |

### Electrical

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 10.0A |
|-------------------------------|-------|

### Physical

|                    |              |
|--------------------|--------------|
| Gender             | Male         |
| Material - Contact | Copper Alloy |
| Material - Plating | Silver       |
| Net Weight         | 0.700/g      |
| Number of Grooves  | 0            |
| Packaging Type     | Bag          |
| Stripping Length   | 8.00mm       |
| Wire Size (AWG)    | 18           |

|                           |      |
|---------------------------|------|
| Wire Size mm <sup>2</sup> | 1.00 |
|---------------------------|------|

---

**Mates With / Use With**

**Mates with Part(s)**

| Description                                     | Part Number  |
|-------------------------------------------------|--------------|
| GWconnect Heavy-Duty Connectors and Accessories | <u>93601</u> |

**Use with Part(s)**

| Description | Part Number                                |
|-------------|--------------------------------------------|
| Use With    | S-D, S-DD, S-K, S-Q, S-QD, and S-M Inserts |