

Northern Technologies
Performance By Design

Big Punch - Small Package!
9 position metal d-sub
w/ large exit

New!

*Handles up to 0.550"
cable diameter!*

*Contact Sales
for detailed information*

From Product Innovation to Product Delivery

Two Piece Metalized Plastic Straight Exit Covers



Two Piece Metalized Plastic Straight Exit Covers

FEATURES	
	exceeds FCC Class A requirements
	compression insert system
	easy assembly
	custom logo available - consult factory
	available in 9, 15, 25, 37 & 50 positions
	CLICK HERE FOR ASSEMBLY INSTRUCTIONS

SPECIFICATIONS:

CAD FILES

Cover Material:	ABS	9 POS. [STP]
Cover Finish:	bright nickel over copper under-plate	15 POS. [STP]
Compression Insert:	thermoplastic - pvc	25 POS. [STP]
Hardware Material:	steel	37 POS. [STP]
Hardware Finish:	zinc plate	50 POS.[STP]

Standard Product Part Numbers with 1/2 Mating Screws

Size	NorTech Logo	NoLogo	Drawings
9 Position (Pkg)	C88E301000	C88E300000	9 POS. DWG.
9 Position (Bulk)	A30E301000	A30E300000	
15 Position (Pkg)	C88E311000	C88E310000	15 POS. DWG.
15 Position (Bulk)	A30E311000	A30E310000	
25 Position (Pkg)	C88E321000	C88E320000	25 POS. DWG.
25 Position (Bulk)	A30E321000	A30E320000	
37 Position (Pkg)	C88E331000**	C88E330000	37 POS. DWG.
37 Position (Bulk)	A30E331000**	A30E330000	
50 Position (Pkg)	C88E341000**	C88E340000	50 POS. DWG.
50 Position (Bulk)	A30E341000**	A30E340000	

Standard Product Part Numbers with 7/16 Mating Screws

Size	NorTech Logo	NoLogo	Drawings
9 Position (Pkg)	C88E3010001	C88E3000001	9 POS. DWG.
9 Position (Bulk)	A30E3010001	A30E3000001	
15 Position (Pkg)	C88E3110001	C88E3100001	15 POS. DWG.
15 Position (Bulk)	A30E3110001	A30E3100001	
25 Position (Pkg)	C88E3210001	C88E3200001	25 POS. DWG.
25 Position (Bulk)	A30E3210001	A30E3200001	
37 Position (Pkg)	C88E3310001**	C88E3300001	37 POS. DWG.
37 Position (Bulk)	A30E3310001**	A30E3300001	
50 Position (Pkg)	C88E3410001**	C88E3400001	50 POS. DWG.
50 Position (Bulk)	A30E3410001**	A30E3400001	

Thumbscrew Version Product Part Numbers

Size	NorTech Logo	NoLogo	Drawings
9 Position (Pkg)	C88E301000T	C88E300000T	9 POS. DWG.
15 Position (Pkg)	C88E311000T	C88E310000T	15 POS. DWG.
25 Position (Pkg)	C88E321000T	C88E320000T	25 POS. DWG.
37 Position (Pkg)	C88E331000T**	C88E330000T	37 POS. DWG.
50 Position (Pkg)	C88E341000T**	C88E340000T	50 POS. DWG.

FRVO Product Part Numbers (UL94V-0)

Size	NorTech Logo	NoLogo	Drawings
9 Position (Pkg)	F88E301000 **	F88E300000 *	9 POS. DWG.
9 Position (Bulk)	F30E301000 **	F30E300000 *	
15 Position (Pkg)	F88E311000 **	F88E310000 *	15 POS. DWG.
15 Position (Bulk)	F30E311000 **	F30E310000 *	
25 Position (Pkg)	F88E321000 **	F88E320000 *	25 POS. DWG.
25 Position (Bulk)	F30E321000 **	F30E320000 *	
37 Position (Pkg)	F88E331000 **	F88E330000 *	37 POS. DWG.
37 Position (Bulk)	F30E331000 **	F30E330000 *	
50 Position (Pkg)	F88E341000 **	F88E340000 *	50 POS. DWG.
50 Position (Bulk)	F30E341000 **	F30E340000 *	

* Contact Customer Service For Availability

**Special Order Item – Minimum Order Quantity Applies

Products

- View All Products
- Product Search
- Cross Reference

About Us

- About Us
- Contact Us
- Legal

Partners

- Distributors
- Representatives

Recent News

- July 1st & July 4th 2017 Holiday Schedule



Facebook



Newsletter

