

[All Categories](#) > [Sensing](#) > [Proximity Sensors](#) > [Special Models for Proximity Sensors](#) > [E2EQ](#) > Item # E2EQ-X10D2R-M1TGJ-T4-US 0.3M

Item # E2EQ-X10D2R-M1TGJ-T4-US 0.3M, E2EQ Series 10 mm Sensing Distance Proximity Sensor with Polyvinyl Chloride (PVC) Flame-Resistant Cable and M12 Connector on a 0.3 m Pigtail

Request Information

[Printable Page](#) [Download PDF](#) [Email This Page](#)



Prox. Sensor

DOWNLOADS

- [E2EQ Weld Spatter Resistant Proximity Sensor Data Sheet](#)
- [E2EQ Spatter Resistant Cylindrical Inductive Proximity Sensor Datasheet](#)

Specifications

Type	Proximity Sensor
Output Type	2-Wire Direct Current (DC)
Sensor Type	Inductive
Range	0 to 10 mm
DC Voltage	12 to 24 V
Dependencies	XS2FM3
Accessories	Y92E-B30, Y92E-SUMB-30, Y92E-GS30, Y92E-GS30-SS, Y92E-GSB30, Y92E-ES30, Y92E-G30S, Y92E-G30S-T, Y92E-EG30-T, Y92E-SC30-T, Y92E-SC30-C, Y92E-E30, Y92E-CF30, Y92E-E30-2, Y92E-B30MT, Y92E-B30FS, Y92E-B30FRAS, Y92E-B30AS, Y92E-B30RAS, Y92E-WJ12X36IN, Y92E-WJ34X36IN, Y92E-WJ12X25FT, Y92E-WJ34X25FT, Y92E-WJ12X50FT, Y92E-WJ34X50FT, E39-VA
Special Function	Weld Spatter-Resistant Fluororesin Coated Proximity Sensor
Shield Type	Shielded
Contact Configuration	Normally Closed (NC)
Case Material	Fluororesin Coated Brass
Threaded Length	38 mm
Overall Length	56 mm
Mounting	Bracket with 30 mm Mounting Hole or M30x1.5 Threaded Hole

Mounting Hole Size	30 mm
Electrical Connection	Polyvinyl Chloride (PVC) Flame-Resistant Cable with M12 Connector on a 0.3 m Pigtail
Sensing Distance	10 mm

News

- [Product News](#)
- [Corporate News](#)
- [Omron on Social Media](#)
- [eNews](#)

Company Info

- [About Omron](#)
- [Omron Principles](#)
- [Company Profile](#)
- [Business Fields](#)
- [Events](#)
- [Giving Back](#)
- [Environmental](#)





Careers

- [Awards](#)
- [Giving Back](#)
- [Summer Internships](#)

Contact

- [Omron in United States](#)
- [Contact Us](#)
- [Global presence](#)

Follow us

-  [Facebook](#)
-  [Twitter](#)
-  [LinkedIn](#)
-  [Youtube](#)