

**TE CONNECTIVITY (TE)**  
**V23601A1127E 1=LP-STECKER**

✓ ACTIVE

1-1393662-2

TE Internal Number: 1-1393662-2

Alias ID: V23601A1127E 1, V23601A1127E1

[Get a Sample](#)

[Compatible Parts & Tooling](#)

↓ [PRODUCT DRAWING](#)  
English

↓ [3D PDF](#)

> [See All Documentation](#)

[Add to List](#) ▼ ▼ | [Documents](#) | [Features](#) | [Compliance](#) | [Similar Products](#)

North America ▼

DISTRIBUTOR	PHONE	STOCK	DATE AS OF	
<a href="#">AVNET ELECTRONICS</a>	480-643-2000	1,658	2018/01/09	<a href="#">Visit Site</a>
<a href="#">MASTER ELECTRONICS CORP.</a>	1-888-473-5297	113	2018/01/07	<a href="#">Visit Site</a>

[View More Distributors \(2\)](#)

[DOCUMENTATION](#)

[FEATURES](#)

[PRODUCT COMPLIANCE](#)

Product Drawings

[Bulkhead Angle Plug 1.0/2.3 Insert 50 Ohm With PCB Connection](#)

PDF **(TIFF AVAILABLE)**

**English**

CAD Files

[3D PDF](#)

PDF

**3D**

[Customer View Model](#)

2D\_DXF.ZIP

**English**

[Customer View Model](#)

3D\_IGS.ZIP

**English**

[Customer View Model](#)

3D\_STP.ZIP

## Catalog Pages/Data Sheets

[DIN Inserts](#)

PDF

English

## Product Environmental Compliance

TE Material Declaration

[MD\\_1-1393662-2\\_07032014830\\_dmtec](#)

PDF

English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

## Product Type Features

Connector System

**Cable-to-Board**

Sealable

**No**

Connector &amp; Contact Terminates To

**Printed Circuit Board**

PCB Mounting Orientation

**Vertical**

Dielectric Material

**PTFE**

Product Type

**Contact Insert**

Connector Type

**Coaxial Contacts**

## Electrical Characteristics

Impedance ( $\Omega$ )**50, 75**

## Body Features

Body Style

**Right Angle**

## Contact Features

Center Contact Material

**Brass**

Contact Type

**Pin**

Center Contact Plating Material

**Gold**

Mating Contact Retention

**Without**

Contact Style

**Captivated**

## Mechanical Attachment

Panel Mount Feature Type

**Bulkhead**

Connector Mounting Type

**Board Mount**

## Operation/Application

For Use With

**SIEDECON Female Connectors**

Circuit Application

**Power & Signal**

Packaging Features

Packaging Method

**Tray**

Packaging Quantity

**100**

Statement of Compliance

[Statement of Compliance](#)

PDF

Compatible Products

[> Contact Product Support](#)


Customers Also Bought

TO-5/.100 GRID RELAYS




**MGSC-26W=MGS .100  
GRID RELAY**  
MGSC-26W

POWER CONTACTS



**C42334A 347A 93=HS-  
STECKER**  
1393589-5

CIRCULAR CONNECTOR SEALS



**ECONOSEAL FLANGE,  
GASKET**  
81665-1

SIGNAL RELAYS



**IMB06CGR 140mW 12V  
DIELEC.2500**  
1462041-3

About TE Connectivity

For Partners

Customer Support

**CALL US**

**LIVE CHAT**

United States

Our Company

Events

TE News Center

Careers

Investors

Corporate Responsibility

Terms and Conditions of  
Sale

Distributors

Suppliers

Email or Call Us

Find Authorized Distributors

What's New on TE.com

Product FAQs

Select Country & Language

United States (EN)

Germany (DE)

China (中文)

Japan (日本語)

Afghanistan (EN) ▼

Find Your Country ▼

[Terms of Use](#) | [Privacy](#) | [Cookie Policy](#) | [Accessibility](#) | [Site Map](#)



© 2018 TE Connectivity. All Rights Reserved.