

## Marking foil for zack marker strip - TML (104X3,8)R - 0801833

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Marking foil for zack marker strip, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, THERMOMARK ROLL X1, Mounting type: Adhesive, Lettering field: 104 x 3.8 mm

### Product Features

- Self-adhesive marker strips for terminal blocks without marker groove, continuous
- Labeling service: Phoenix Contact can custom-label all TML markers according to your requirements
- The markers that are supplied in roll format can be labeled quickly and cost-effectively using THERMOMARK printers

### Key Commercial Data

|                                      |          |
|--------------------------------------|----------|
| Packing unit                         | 1 pc     |
| Weight per Piece (excluding packing) | 520.0 g  |
| Custom tariff number                 | 39199000 |
| Country of origin                    | Germany  |

### Technical data

#### Dimensions

|            |        |
|------------|--------|
| Length (b) | 104 mm |
| Width (a)  | 3.8 mm |

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 150 °C |
|---------------------------------|-------------------|

#### General

|                                     |                                |
|-------------------------------------|--------------------------------|
| Color                               | white                          |
| Components                          | free from silicone and halogen |
| Material                            | Polyester                      |
| Wipe resistance                     | DIN EN 61010-1 (VDE 0411-1)    |
| Number of individual labels         | 2500                           |
| Number of individual labels per row | 1                              |
| Marking mounting type               | Adhesive                       |

### Standards and Regulations

## Marking foil for zack marker strip - TML (104X3,8)R - 0801833

### Technical data

#### Standards and Regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190208 |
| eCl@ss 4.1 | 24190208 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27149129 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC001288 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39121410 |