

Marker pin Zack strip - BN-ZB 5/WH:UNBEDRUCKT - 1400078


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Marker pin Zack strip, Strip, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, mounting type: plug in, for terminal block width: 5 mm, lettering field size: 4 x 4 mm, Number of individual labels: 10



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 020118
GTIN	4017918020118
Weight per Piece (excluding packing)	0.480 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Width (a)	4 mm
-----------	------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

General

Note	Can be labeled with CMS
Color	white
Type	high
Components	free from silicone and halogen
Flammability rating according to UL 94	V2

Marker pin Zack strip - BN-ZB 5/WH:UNBEDRUCKT - 1400078

Technical data

General

Material	PA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	10
Number of individual labels per row	10
Number of marker strips	10
Marking mounting type	plug in

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V2

Classifications

eCl@ss

eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137
eCl@ss 9.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761
ETIM 6.0	EC000761
ETIM 7.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131505
UNSPSC 18.0	39131505

Marker pin Zack strip - BN-ZB 5/WH:UNBEDRUCKT - 1400078

Classifications

UNSPSC

UNSPSC 19.0	39131505
UNSPSC 20.0	39131505
UNSPSC 21.0	39131505