

# Screwdriver - SF-SLIC 1,6X10-175



1212555

<https://www.phoenixcontact.com/us/products/1212555>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Screwdriver, slot-headed, with impact cap, with hexagon wrench aid for open-end wrench and ring wrench, size: 1.6 x 10 x 175 mm, 2-component grip

## Your advantages

- The tools feature ergonomic two-component safety handles
- Large contact surface of blades inside screw head

## Commercial Data

Item number	1212555
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to Order (non-returnable)
Sales Key	B14
Product Key	BH3141
Catalog Page	Page 443 (C-3-2019)
GTIN	4046356589901
Weight per Piece (including packing)	229.43 g
Weight per Piece (excluding packing)	229.43 g
Customs tariff number	82054000
Country of origin	CZ

# Screwdriver - SF-SLIC 1,6X10-175



1212555

<https://www.phoenixcontact.com/us/products/1212555>

## Technical Data

### Notes

#### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

### Product properties

Type	Bladed
Product type	Screwdriver tools
Type	straight

### Connection data

Output	Bladed
--------	--------

### Dimensions

Width	40 mm
Blade width	10 mm
Blade height	175 mm
Length	287 mm
Wrench size	0 mm
Blade thickness	1.6 mm

### Material specifications

Material	alloyed tool steel
----------	--------------------

### Standards and regulations

Tests	DIN 5263
-------	----------

### Mounting

Wrench size	0 mm
-------------	------

# Screwdriver - SF-SLIC 1,6X10-175



1212555

<https://www.phoenixcontact.com/us/products/1212555>

## Approvals



**EAC**

Approval ID: RU C-DE.AI30.B.01750

# Screwdriver - SF-SLIC 1,6X10-175



1212555

<https://www.phoenixcontact.com/us/products/1212555>

## Classifications

### ECLASS

ECLASS-9.0	21040407
ECLASS-10.0.1	21040407
ECLASS-11.0	21040407

### ETIM

ETIM 8.0	EC000158
----------	----------

### UNSPSC

UNSPSC 21.0	27111700
-------------	----------

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)