

Housing - HC-STA-B10-HHWD-1STM25-EL-AL - 1412608

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Sleeve housing B10, With double locking latch, Material: Die-cast aluminum, salt water resistant, Cable outlets: 1, lateral, Height: 72 mm, Cable gland: none, Gland: no, 1x M25, Standard

Why buy this product

- good shielding in the event of electromagnetic interference



Key Commercial Data

| | |
|----------------------|---|
| Packing unit | 1 STK |
| GTIN |  4 055626 059358 |
| GTIN | 4055626059358 |
| Custom tariff number | 85389099 |
| Country of origin | China |

Technical data

Dimensions

| | |
|--------|-------|
| Height | 72 mm |
| Width | 44 mm |
| Length | 73 mm |

Ambient conditions

| | |
|--|-------------|
| Degree of protection of housing (IP) | IP66 |
| | IP67 |
| Degree of protection of housing (NEMA) | 4 (UL 50e) |
| | 4X (UL 50e) |

Housing - HC-STA-B10-HHWD-1STM25-EL-AL - 1412608

Technical data

Ambient conditions

| | |
|---------------------------------|-------------------|
| | 12 (UL 50e) |
| Ambient temperature (operation) | -40 °C ... 125 °C |

General

| | |
|------------------------------|--|
| Note | For contact inserts HC-B10, BB18, DD42, M, K8/24 |
| Size | B10 |
| Housing type | Sleeve housing |
| Color | silver |
| Locking type | With double locking latch |
| No. of cable outlets | 1 |
| Cable exit | lateral |
| Screw connection | none |
| Type of the screw connection | 1x M25 |
| Housing material | Die-cast aluminum, salt water resistant |
| Housing surface material | Uncoated |
| Material lock | PA |

Approvals


Approvals

Approvals

EAC / GL / UL Recognized / cUL Recognized / cULus Recognized

Ex Approvals

Approval details

| | | |
|-----|---|---------------------|
| EAC |  | 7500651.22.01.00246 |
|-----|---|---------------------|

| | | | |
|----|---|---|------------|
| GL |  | http://exchange.dnv.com/tari/ | 6196614 HH |
|----|---|---|------------|

Housing - HC-STA-B10-HHWD-1STM25-EL-AL - 1412608

Approvals

| | | | |
|---------------|---|---|---------|
| UL Recognized |  | http://database.ul.com/cgi-bin/XYVV/template/LISEXT/1FRAME/index.htm | E255026 |
|---------------|---|---|---------|

| | | | |
|----------------|---|---|---------|
| cUL Recognized |  | http://database.ul.com/cgi-bin/XYVV/template/LISEXT/1FRAME/index.htm | E255026 |
|----------------|---|---|---------|

| | | | |
|------------------|---|---|--|
| cULus Recognized |  | http://database.ul.com/cgi-bin/XYVV/template/LISEXT/1FRAME/index.htm | |
|------------------|---|---|--|