

Housing - HC-STA-B16-HLFD-1STM32-EL-AL



1412718

<https://www.phoenixcontact.com/gb/products/1412718>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Sleeve housing B16, for double locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 1, lateral, 1x M32, height: 60 mm, cable gland: none, Standard

Your advantages

- good shielding in the event of electromagnetic interference

1412718

<https://www.phoenixcontact.com/gb/products/1412718>

Commercial Data

Item number	1412718
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	BF7APB
Product Key	BF7APB
Catalog Page	Page 624 (C-2-2019)
GTIN	4055626059921
Weight per Piece (including packing)	189.9 g
Weight per Piece (excluding packing)	189 g
Customs tariff number	85389099
Country of origin	PL

1412718

<https://www.phoenixcontact.com/gb/products/1412718>

Technical Data


Notes

General	For contact inserts HC-B16, BB32, D40, DD72, HS6, HV6, M, K
---------	---

Product properties

Type	B16
Product type	Housing with locking latch
Application	Standard
No. of cable outlets	1
Type of the screw connection	1x M32
Housing type	Sleeve housing
Locking type	for double locking latch
Cable outlet	lateral
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	44 mm
Height	60 mm
Length	93.5 mm

Material specifications

Color	gray aluminum
Housing surface material	uncoated
Impact strength	IK09
Housing material	Die-cast aluminum, salt water resistant

Ambient conditions

Degree of protection	IP66
	IP67
Degree of protection	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Impact strength	IK09
Ambient temperature (operation)	-40 °C ... 125 °C

Mechanical properties

Mechanical data

Housing - HC-STA-B16-HLFD-1STM32-EL-AL



1412718

<https://www.phoenixcontact.com/gb/products/1412718>

Type of the screw connection	1x M32
Locking type	Pin

Housing - HC-STA-B16-HLFD-1STM32-EL-AL




1412718

<https://www.phoenixcontact.com/gb/products/1412718>

Drawings

Dimensional drawing



Dimensional drawing

1412718

<https://www.phoenixcontact.com/gb/products/1412718>

Approvals

DNV

Approval ID: TAE000037S



cUL Recognized

Approval ID: E255026



UL Recognized

Approval ID: E255026



EAC

Approval ID: RU C-DE.AI30.B.01102



EAC

Approval ID: RU C-DE.BL08.B.00511

cULus Recognized

1412718

<https://www.phoenixcontact.com/gb/products/1412718>

Classifications

ECLASS

ECLASS-9.0	27440202
ECLASS-10.0.1	27440202
ECLASS-11.0	27440202

ETIM

ETIM 8.0	EC000437
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

Housing - HC-STA-B16-HLFD-1STM32-EL-AL



1412718

<https://www.phoenixcontact.com/gb/products/1412718>

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

1412718

<https://www.phoenixcontact.com/gb/products/1412718>

Accessories

Cable gland

Cable gland - G-INS-M32-M68N-NNES-S - 1411166

<https://www.phoenixcontact.com/gb/products/1411166>



Cable gland, cable gland material: Nickel-plated brass, external cable diameter 15 mm ... 21 mm, shielding: no, connecting thread: M32 x 1.5, color: silver, with O-ring

Screw connection

Screw connection - WP-G HF IP66 M32 BK - 3240900

<https://www.phoenixcontact.com/gb/products/3240900>



Cable gland, metric thread, IP66 protection, straight

1412718

<https://www.phoenixcontact.com/gb/products/1412718>

Cable gland

Cable gland - G-INSEC-M32-M68N-NCRS-S - 1411191

<https://www.phoenixcontact.com/gb/products/1411191>



Cable gland, cable gland material: Nickel-plated brass, external cable diameter 14 mm ... 21 mm, shielding: yes, connecting thread: M32 x 1.5, color: silver, with O-ring

Screw connection

Screw connection - WP-G HF IP69K M32 BK - 3240886

<https://www.phoenixcontact.com/gb/products/3240886>



Cable gland, metric thread, IP68/69k protection, straight

Housing - HC-STA-B16-HLFD-1STM32-EL-AL

1412718

<https://www.phoenixcontact.com/gb/products/1412718>

Plastic label

Plastic label - US-EMLP (20X9) CUS - 0830085

<https://www.phoenixcontact.com/gb/products/0830085>

Plastic label, can be ordered: by card, white, labeled according to customer specifications, mounting type: adhesive, lettering field size: 20 x 9 mm, Number of individual labels: 75



Screw connection

Screw connection - WP-GA HF IP66 M32 BK - 3240928

<https://www.phoenixcontact.com/gb/products/3240928>

Cable gland, metric thread, IP66 protection, angled



Housing - HC-STA-B16-HLFD-1STM32-EL-AL

1412718

<https://www.phoenixcontact.com/gb/products/1412718>

Protective cover

Protective cover - HC-B16-HCLWD-PLR-BK - 1414639

<https://www.phoenixcontact.com/gb/products/1414639>



Protective cover B16, with double locking latch, protective cover material: PA, height: 21.6 mm, seal: yes, diameter of retaining cord eyelet: 30 mm

Screw connection

Screw connection - WP-GA HF IP69K M32 BK - 3240914

<https://www.phoenixcontact.com/gb/products/3240914>



Cable gland, metric thread, IP68/69k protection, angled

Housing - HC-STA-B16-HLFD-1STM32-EL-AL

1412718

<https://www.phoenixcontact.com/gb/products/1412718>

Screw connection

Screw connection - WP-GR HF IP66 M32 BK - 3240956

<https://www.phoenixcontact.com/gb/products/3240956>



Cable gland, metric thread, IP66 protection, with strain relief

Screw connection

Screw connection - WP-GR HF IP69K M32 BK - 3240942

<https://www.phoenixcontact.com/gb/products/3240942>



Cable gland, metric thread, IP68/69k protection, with strain relief

Housing - HC-STA-B16-HLFD-1STM32-EL-AL

1412718

<https://www.phoenixcontact.com/gb/products/1412718>

Screw connection

Screw connection - WP-G PP HF M32 - 3241000

<https://www.phoenixcontact.com/gb/products/3241000>



Cable gland made from PP with metric thread, IP65 protection

Screw connection

Screw connection - WP-GT PP HF M32 - 3241014

<https://www.phoenixcontact.com/gb/products/3241014>



Cable gland made from PP with metric thread, rotatable, IP54 protection

Housing - HC-STA-B16-HLFD-1STM32-EL-AL

1412718

<https://www.phoenixcontact.com/gb/products/1412718>

Screw connection

Screw connection - WP-G BRASS IP40 M32 - 3241049

<https://www.phoenixcontact.com/gb/products/3241049>



Cable gland made from brass with metric thread, IP40 protection

Screw connection

Screw connection - WP-GT BRASS M32 - 3241035

<https://www.phoenixcontact.com/gb/products/3241035>



Cable gland made from brass with metric thread, rotatable, IP40 protection

Housing - HC-STA-B16-HLFD-1STM32-EL-AL



1412718

<https://www.phoenixcontact.com/gb/products/1412718>

Screw connection

Screw connection - WP-G BRASS IP65 M32 - 3241063

<https://www.phoenixcontact.com/gb/products/3241063>



Cable gland made from brass with metric thread, IP65 protection

Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

info@phoenixcontact.co.uk