

## Adapter - HC-B-TA-M32-ER-AL - 1414258

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Adapter, aluminum, for EVO housing, M32 thread



### Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 022208
GTIN	4055626022208
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### Dimensions

Length of internal thread	13 mm
---------------------------	-------

#### Ambient conditions

Degree of protection	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Ambient temperature (operation)	-40 °C ... 125 °C

#### General

Material	Die-cast aluminum, corrosion-resistant
Housing material	Die-cast aluminum, corrosion resistant
Thread type on connection side	Bayonet B metal

# Adapter - HC-B-TA-M32-ER-AL - 1414258


## Technical data

### General

Thread type on seal side	M32
Torque	18 Nm (Tightening torque of screw connection to be screwed in)

## Drawings

Dimensional drawing



Dimensional drawing

## Classifications

### eCl@ss

eCl@ss 5.1	27143424
eCl@ss 6.0	27261207
eCl@ss 8.0	27440209
eCl@ss 9.0	27440209

### ETIM

ETIM 5.0	EC002635
ETIM 6.0	EC002635

### UNSPSC

UNSPSC 13.2	39121408
-------------	----------

## Approvals

### Approvals

Approvals

EAC / UL Recognized / cUL Recognized / cULus Recognized





# Adapter - HC-B-TA-M32-ER-AL - 1414258

## Approvals

Ex Approvals

---

### Approval details

EAC			7500651.22.01.00246
UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	E255026
cUL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	E255026
cULus Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	