

Cable gland - G-INS-M32-S68N-NNES-S - 1424528


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland, Cable gland material: Nickel-plated brass, External cable diameter 13 mm ... 18 mm, Shielding: No, Connecting thread: M32, Color: silver



Key Commercial Data

Packing unit	1
GTIN	 4 055626 374338
GTIN	4055626374338
Custom tariff number	39269097

Technical data

Dimensions

Length	42 mm
Wrench size, union nut	30 mm
Wrench size, support	34 mm
Hexagon angular dimension	37 mm
Length of the connecting thread	9 mm
Feed-through hole diameter	32.1 mm ... 32.3 mm
External cable diameter	13 mm ... 18 mm
	13 mm ... 18 mm (for UL 514 B)

Ambient conditions

Degree of protection	IP69
	IP68 (5 bar, 30 min.)
	IP66
Ambient temperature (operation)	-20 °C ... 100 °C (static)

Cable gland - G-INS-M32-S68N-NNES-S - 1424528


Technical data

General

No. of conductors	1
Cable gland material	Nickel-plated brass
Material, insert	Polyamide 6
Cable seal material	Neoprene
Shielded	No
Thread type on connection side	M32
Thread pitch	1.5 mm
Torque	8 Nm (Union nut) 8 Nm (Support)
	17 Nm (for UL514 B: union nut / support)
Color	silver
Impact category	6
Execution of the strain relief	A
Assembly instructions	1) Mount screw connection support in the housing using the correct torque 2) Insert cable 3) Tighten union nut using the correct torque
Manufacturer	BIMED
Manufacturer Designation	BMBC-04

Drawings

Dimensional drawing



Dimensional drawing

Classifications

eCl@ss

eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

Cable gland - G-INS-M32-S68N-NNES-S - 1424528

Classifications

eCl@ss

eCl@ss 9.0	27144432
------------	----------

ETIM

ETIM 5.0	EC000441
----------	----------

Approvals

Approvals

Approvals

UL Listed / cUL Listed / EAC / cULus Listed

Ex Approvals

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E199260
-----------	--	---	---------

cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E199260
------------	--	---	---------

EAC		EAC-Zulassung
-----	--	---------------

cULus Listed	
--------------	--

Accessories

Accessories

Flat nut

Cable gland - G-INS-M32-S68N-NNES-S - 1424528

Accessories

Nut - A-INL-M32-N-S - 1411244



Nut, Nickel-plated brass, for threads M32, Color: silver

Sealing plugs

Closing cap - SEALING PLUG 17X17 RD - 1421861



Closing cap, PA, Color: red