

## Crimp contact - RC-22P2000 - 1603321

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimp contact, rolled, Single contact, contact diameter: 1 mm, crimp range: 0.22 mm<sup>2</sup> ... 0.56 mm<sup>2</sup>


The figure shows a similar product

### Your advantages

- ✓ Crimping connection: vibration- and temperature-resistant assembly
- ✓ High tensile strength of the connection
- ✓ Low contact resistance
- ✓ Easy production monitoring
- ✓ Variable production run startup, thanks to full or semi-automation



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	100 pc
GTIN	 4 046356 244909
GTIN	4046356244909
Weight per Piece (excluding packing)	1.040 g
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### General

Contact type	rolled
Note	Single contact
Contact diameter	1 mm

# Crimp contact - RC-22P2000 - 1603321

## Technical data

### General


Type of contact	Pin
Connection method	Crimp connection
Insertion/withdrawal cycles mechanical	100
Litz wire cross section min.	0.22 mm <sup>2</sup>
Litz wire cross section max.	0.56 mm <sup>2</sup>
Contact material	Copper alloy
Contact surface	Nickel-plated (Ni), with gold coating (Au)

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Drawings

Dimensional drawing



Dimensional drawing

## Classifications

### eCl@ss

eCl@ss 10.0.1	27440204
eCl@ss 4.0	27260700
eCl@ss 4.1	27260700
eCl@ss 5.0	27260700
eCl@ss 5.1	27261200
eCl@ss 6.0	27261200
eCl@ss 7.0	27440204
eCl@ss 8.0	27440204
eCl@ss 9.0	27440204

# Crimp contact - RC-22P2000 - 1603321

## Classifications

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC000796
ETIM 5.0	EC000796
ETIM 6.0	EC000796
ETIM 7.0	EC000796

### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	39121522
UNSPSC 18.0	39121522
UNSPSC 19.0	39121522
UNSPSC 20.0	39121522
UNSPSC 21.0	39121522

## Approvals

### Approvals

---

### Approvals


### EAC

---

### Ex Approvals

---

### Approval details

EAC		B.01742
-----	---	---------

## Accessories

### Accessories

### Crimping tool

## Crimp contact - RC-22P2000 - 1603321

### Accessories

Crimping pliers - RC-Z2130 - 1604267



Crimping pliers for rolled RC crimp contacts  $\varnothing$  1 mm, litz wire cross section of 0.08 mm<sup>2</sup> ... 0.56 mm<sup>2</sup>

---

---