

## Crimp contact - SL-1CKS050 - 1607920

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimp contact, turned, contact diameter: 10 mm, crimp range: 50 mm<sup>2</sup> ... 50 mm<sup>2</sup>

The figure may differ depending on the connection area

### Why buy this product

- Crimping connection: vibration- and temperature-resistant assembly
- High tensile strength of the connection
- Low contact resistance
- Easy production monitoring

### Key Commercial Data

Packing unit	1 STK
Minimum order quantity	4 STK
GTIN	 4 046356 272919
GTIN	4046356272919
Weight per Piece (excluding packing)	1.000 g
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### General

Contact type	turned
Contact diameter	10 mm
Type of contact	Socket
Connection method	Crimp connection

# Crimp contact - SL-1CKS050 - 1607920

## Technical data

### General


Insertion/withdrawal cycles mechanical	100
Litz wire cross section min.	50 mm <sup>2</sup>
Litz wire cross section max.	50 mm <sup>2</sup>
Contact material	Copper alloy
Contact surface	Silver

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Drawings

Dimensional drawing



## Classifications

### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260708
eCl@ss 7.0	27440312
eCl@ss 8.0	27440204
eCl@ss 9.0	27440204

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC000796
ETIM 5.0	EC000796
ETIM 6.0	EC000796

## Crimp contact - SL-1CKS050 - 1607920

### Classifications

#### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	39121522

### Accessories

#### Accessories

##### Crimping tool

Electrohydraulic crimping tool - SL-Z0007 - 1613484



Electrohydraulic crimping tool

---

Crimping stamp - SL-Z0015 - 1613492



Crimping stamp