

Adapter - HC-NPT-1/2-M20 - 1686847

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



NPT adapter, IP68, up to 5 bar, incl. O-ring seal, M20 to 1/2"



Key Commercial Data

| | |
|--------------------------------------|----------|
| Packing unit | 1 pc |
| Weight per Piece (excluding packing) | 34.44 g |
| Custom tariff number | 74199990 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|----------------------------------|---------|
| Length | 25 mm |
| Length without connecting thread | 18.5 mm |
| Connecting thread diameter | 20 mm |
| Wrench size, union nut | 24 mm |
| Hexagon angular dimension GRP | 24 mm |
| Length of the connecting thread | 6.5 mm |

Ambient conditions

| | |
|---------------------------------|---|
| Degree of protection | IP68 (Depends on the screw connection used) |
| Ambient temperature (operation) | -20 °C ... 80 °C |

General

| | |
|--------------------------------|---------------------|
| Material | Nickel-plated brass |
| Cable gland material | Nickel-plated brass |
| O-ring material | NBR |
| Thread type on connection side | M20 |
| Thread type on seal side | 1/2-inch NPT |

Adapter - HC-NPT-1/2-M20 - 1686847

Technical data

General

| | |
|-------|--------|
| Color | silver |
|-------|--------|

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27141209 |
| eCl@ss 4.1 | 27141209 |
| eCl@ss 5.0 | 27149109 |
| eCl@ss 5.1 | 27149109 |
| eCl@ss 6.0 | 27149109 |
| eCl@ss 7.0 | 27149109 |
| eCl@ss 8.0 | 27439207 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000441 |
| ETIM 3.0 | EC000441 |
| ETIM 4.0 | EC000441 |
| ETIM 5.0 | EC000938 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 31261502 |
| UNSPSC 7.0901 | 31261502 |
| UNSPSC 11 | 31261502 |
| UNSPSC 12.01 | 31261502 |
| UNSPSC 13.2 | 31261502 |

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Adapter - HC-NPT-1/2-M20 - 1686847


Approvals

Approval details

EAC

Drawings

Dimensional drawing



Dimensional drawing

