

Housing - HC-D 7-TFL-48/M1PG11S - 1773271

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Sleeve housing, for single locking latch, height 48 mm, with screw connection, 1 x Pg11, lateral cable outlet, zinc die-cast



Key Commercial Data

| | |
|--------------------------------------|--|
| Packing unit | 1 pc |
| GTIN |  4 017918 122270 |
| Weight per Piece (excluding packing) | 73.78 g |
| Custom tariff number | 85389099 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|-------------------------|--------------------|
| Height | 48 mm |
| Width | 28 mm |
| Length | 26.5 mm |
| Wrench size, union nut | 18 mm |
| External cable diameter | 7.5 mm ... 12.5 mm |

Ambient conditions

| | |
|--------------------------------------|---------------------------|
| Degree of protection of housing (IP) | IP54 |
| | IP65 (with sealing screw) |
| Ambient temperature (operation) | -40 °C ... 125 °C |

General

| | |
|------|---|
| Note | For contact inserts HC-D7, D8, A3, A4, B5, HS2-D7 |
| Size | D7 |

Housing - HC-D 7-TFL-48/M1PG11S - 1773271

Technical data

General

| | |
|------------------------------|--------------------------|
| Housing type | Sleeve housing |
| Locking type | for single locking latch |
| No. of cable outlets | 1 |
| Cable exit | Lateral |
| Screw connection | with |
| Type of the screw connection | 1x Pg11 |
| Housing material | Zinc die-cast |
| Housing surface material | Powder-coated, gray |
| Cable gland material | Nickel-plated brass |
| Cable seal material | NBR |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27140816 |
| eCl@ss 4.1 | 27140816 |
| eCl@ss 5.0 | 27143424 |
| eCl@ss 5.1 | 27143424 |
| eCl@ss 6.0 | 27143424 |
| eCl@ss 7.0 | 27440209 |
| eCl@ss 8.0 | 27440202 |
| eCl@ss 9.0 | 27440202 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000437 |
| ETIM 3.0 | EC000437 |
| ETIM 4.0 | EC000437 |
| ETIM 5.0 | EC000437 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 31261502 |
| UNSPSC 7.0901 | 31261502 |
| UNSPSC 11 | 31261502 |
| UNSPSC 12.01 | 31261502 |
| UNSPSC 13.2 | 31261502 |

Approvals

Approvals

Housing - HC-D 7-TFL-48/M1PG11S - 1773271

Approvals

Approvals

EAC / GL

Ex Approvals

Approvals submitted

Approval details

| |
|-----|
| EAC |
|-----|

| |
|----|
| GL |
|----|

Drawings

Dimensional drawing

