

Cable gland - VC-K-KV-PG21 4X8 - 1885606

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Half screw connection Pg21, made of plastic, consisting of rubber seal with several holes (4 x 8 mm) and one pressure screw, for type 2 - 4 housings



Key Commercial Data

Packing unit	1 STK
Minimum order quantity	5 STK
GTIN	 4 017918 176709
GTIN	4017918176709
Weight per Piece (excluding packing)	15.310 g
Custom tariff number	39269097
Country of origin	Poland

Technical data

Dimensions

Wrench size, union nut	33 mm
External cable diameter	7.5 mm ... 8 mm (Cable 1)
	7.5 mm ... 8 mm (Cable 2)
	7.5 mm ... 8 mm (Cable 3)
	7.5 mm ... 8 mm (Cable 4)

Ambient conditions

Degree of protection	IP65
	IP65
Ambient temperature (operation)	-20 °C ... 100 °C

Cable gland - VC-K-KV-PG21 4X8 - 1885606

Technical data

General

Type of the screw connection	Half screw connection
No. of conductors	4
Material, pressure screw	Polyamide
Seal material	TPE
Shielded	no
Thread type on seal side	Pg21
Tightening torque, union nut	7.50 Nm

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109
eCl@ss 9.0	27144432

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441
ETIM 6.0	EC000441

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	39121311

Cable gland - VC-K-KV-PG21 4X8 - 1885606

Approvals


Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		B.01742
-----	---	---------

Accessories

Accessories

Half screw connection

Cable gland - VC-K-KV-PG21-O - 1885363

Half screw connection made of plastic with rubber seal without hole or for individual holes
