

T distributor - PLD E 608-CO-MS/FS/FR - 2702310

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



T-distributor with 2 sockets and one connector for series connection, black, 3-pos.



Key Commercial Data

Packing unit	1 STK
Minimum order quantity	5 STK
GTIN	 4 055626 113364
GTIN	4055626113364
Weight per Piece (excluding packing)	28.000 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

General

Design	T-distributor
Color	black
Number of positions	3
Note number of positions	2+PE

Ambient conditions

Degree of protection	IP20
	IP40 (plugged in)
Ambient temperature (operation)	70 °C
Ambient temperature (storage/transport)	-30 °C ... 70 °C

T distributor - PLD E 608-CO-MS/FS/FR - 2702310

Technical data

Electrical characteristics

Rated current	16 A (according to EN 61984 at 70°C)
Rated voltage (I/2)	250 V
Rated surge voltage (I/2)	2.5 kV

Mechanical characteristics

QUICKON connectability	5 (according to EN 61984)
Insertion/withdrawal cycles	10 (according to EN 61984)

Material data

Contact material	Brass
Contact surface material	surface-protected
Flammability rating according to UL 94	V2
Degree of pollution	2

Standards and Regulations

Flammability rating according to UL 94	V2
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 5.1	27260702
eCl@ss 8.0	27440102
eCl@ss 9.0	27440103

ETIM

ETIM 5.0	EC002635
ETIM 6.0	EC002061

UNSPSC

UNSPSC 13.2	39121413
-------------	----------

Approvals

Approvals

T distributor - PLD E 608-CO-MS/FS/FR - 2702310




Approvals

Approvals

UL Recognized / cUL Recognized / cULus Recognized

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 118976
cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 118976
cULus Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	
