

Plug-in bridge - FBSR 4-5 - 3001592


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Plug-in bridge, pitch: 5.2 mm, number of positions: 4, color: red



Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 1 STK |
| Minimum order quantity | 50 STK |
| GTIN |  4 046356 890847 |
| GTIN | 4046356890847 |
| Weight per Piece (excluding packing) | 1.500 g |
| Custom tariff number | 85366990 |
| Country of origin | China |

Technical data

Technical data

| | |
|--|---|
| Color | red |
| Material | Copper |
| Number of positions | 4 |
| Pitch | 5.2 mm |
| Flammability rating according to UL 94 | V0 |
| Maximum load current | 17.5 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.) |

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

Plug-in bridge - FBSR 4-5 - 3001592

Technical data

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27141199 |
| eCl@ss 4.1 | 27141199 |
| eCl@ss 5.0 | 27141140 |
| eCl@ss 5.1 | 27141140 |
| eCl@ss 6.0 | 27141140 |
| eCl@ss 7.0 | 27141140 |
| eCl@ss 8.0 | 27141140 |
| eCl@ss 9.0 | 27141140 |

ETIM

| | |
|----------|----------|
| ETIM 4.0 | EC000489 |
| ETIM 5.0 | EC000489 |
| ETIM 6.0 | EC000489 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211829 |
| UNSPSC 7.0901 | 39121426 |
| UNSPSC 11 | 39121426 |
| UNSPSC 12.01 | 39121426 |
| UNSPSC 13.2 | 39121426 |

Approvals

Approvals

Approvals

EAC

Ex Approvals

Plug-in bridge - FBSR 4-5 - 3001592

Approvals

Approval details

| | | |
|-----|---|---------------|
| EAC |  | EAC-Zulassung |
|-----|---|---------------|

Accessories

Accessories

Cutting tools

Front cutter - CUTFOX-FBS - 1212124



Cutting tool, for separating individual jumper bars from FBS ... plug-in bridges and EB ... insertion bridges

Protective cap

Protective cap - FBSC - 3012325



Covering hood, provides reliable shock protection when using cut-to-length FBS ...-5 and FBS ...-6 bridges, color: red