

Connector - C-SCFI 1,5/4,8X0,5



3240050

<https://www.phoenixcontact.com/us/products/3240050>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Slip-on sleeve, red, 0.5 ... 1.5 mm², 4.8 x 0.5

Your advantages

- "Easy Entry" for easy and reliable conductor entry
- Halogen-free
- Hard-soldered crimping zone for maximum pull-out forces
- Electrogalvanized

Commercial Data

Item number	3240050
Packing unit	1 pc
Minimum order quantity	100 pc
Sales Key	B16
Product Key	BH3451
Catalog Page	Page 499 (C-3-2019)
GTIN	4046356452687
Weight per Piece (including packing)	0.851 g
Weight per Piece (excluding packing)	0.851 g
Customs tariff number	85366990
Country of origin	CN

Connector - C-SCFI 1,5/4,8X0,5

3240050

<https://www.phoenixcontact.com/us/products/3240050>

Technical Data


Product properties

Product type	Connector
--------------	-----------

Electrical properties

Fuse	yes
------	-----

Dimensions

Dimensional drawing	
Width	4.8 mm
Length	19.5 mm
Length of the insulating material sleeve	10.5 mm
Maximum stripping length	7 mm
Min. material thickness	0.4 mm
Inner dimensions of the insulating collar	4.1 mm

Material specifications

Color	red
Material	Brass
Flammability rating according to UL 94	V2
Coating	tin-plated
Insulating material	PA
Components	halogen-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 105 °C
---------------------------------	-------------------

Connector - C-SCFI 1,5/4,8X0,5


3240050

<https://www.phoenixcontact.com/us/products/3240050>



Drawings

Dimensional drawing



Connector - C-SCFI 1,5/4,8X0,5



3240050

<https://www.phoenixcontact.com/us/products/3240050>

Classifications

ECLASS

ECLASS-9.0	27400204
ECLASS-10.0.1	27400204
ECLASS-11.0	27400204

ETIM

ETIM 8.0	EC001052
----------	----------

UNSPSC

UNSPSC 21.0	27121700
-------------	----------

Connector - C-SCFI 1,5/4,8X0,5

3240050

<https://www.phoenixcontact.com/us/products/3240050>



Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Connector - C-SCFI 1,5/4,8X0,5

3240050

<https://www.phoenixcontact.com/us/products/3240050>



Accessories

Crimping pliers

Crimping pliers - CRIMPFOX-RCI 2,5 - 1212053

<https://www.phoenixcontact.com/us/products/1212053>



Crimping pliers, for insulated cable lugs, 0.5 mm² ... 2.5 mm² (red, blue), oval crimp

Crimping pliers

Crimping pliers - CRIMPFOX-RCI 2,5-M - 1212728

<https://www.phoenixcontact.com/us/products/1212728>



Crimping pliers, compact pliers, for insulated cable lugs (red, blue), two marked die stations, unlockable pressure lock, lateral entry

Connector - C-SCFI 1,5/4,8X0,5

3240050

<https://www.phoenixcontact.com/us/products/3240050>



Crimping pliers

Crimping pliers - CRIMPFOX-RCI 6 - 1212057

<https://www.phoenixcontact.com/us/products/1212057>



Crimping pliers, for insulated cable lugs, 0.5 mm² ... 6.0 mm² (red, blue, yellow), oval crimp, symmetrical

Crimping pliers

Crimping pliers - CRIMPFOX-RCI 6-1 - 1212059

<https://www.phoenixcontact.com/us/products/1212059>



Crimping pliers, for insulated cable lugs, 0.5 mm² ... 6.0 mm² (red, blue, yellow), oval crimp, asymmetrical

Connector - C-SCFI 1,5/4,8X0,5

3240050

<https://www.phoenixcontact.com/us/products/3240050>

Crimping pliers

Crimping pliers - CRIMPFOX-RCI 6-M - 1212730

<https://www.phoenixcontact.com/us/products/1212730>



Crimping pliers, compact pliers, for symmetrical insulated cable lugs, 0.5 mm² ... 6.0 mm² (red, blue, yellow), three marked die stations, unlockable pressure lock, lateral entry

Crimp insert

Crimp insert - CF 500/DIE RCI 1,5 - 1212263

<https://www.phoenixcontact.com/us/products/1212263>



Die for crimping machine CF 500, for insulated cable lugs (C-RCI... and C-FCI...)
0.14 ... 1.5 mm²

Connector - C-SCFI 1,5/4,8X0,5

3240050

<https://www.phoenixcontact.com/us/products/3240050>



Crimp insert

Crimp insert - CF 500/DIE RCI 6 - 1212240

<https://www.phoenixcontact.com/us/products/1212240>



Die for crimping machine CF 500, for insulated cable lugs (C ... RCI... and C ... FCI...) 0.5 ... 6 mm²

Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com