

## Ring cable lug - C-RC 25/M12 DIN - 3240103

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Ring cable lug, non-insulated, 25 mm<sup>2</sup>, M12

### Your advantages

- ✓ The CRIMPFOX-RC... tools from our CRIMPFOX range of crimping pliers are available for optimum crimping
- ✓ The ring cable lugs without plastic sleeve are made from high-quality tin-plated electrolytic copper for maximum protection against corrosion
- ✓ The hard-soldered press zone enables maximum conductor pull-out values to be achieved

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	100 pc
GTIN	 4 046356 453202
GTIN	4046356453202
Weight per Piece (excluding packing)	10.000 g
Custom tariff number	85369010
Country of origin	China

### Technical data

#### Dimensions

Length (b)	42 mm
Width (a)	31 mm
Maximum stripping length	14 mm
Length of insulation sleeve (c)	11 mm
Inner dimension of the insulating collar (d)	7.5 mm
Distance between the center and the insulation sleeve (e)	20 mm

# Ring cable lug - C-RC 25/M12 DIN - 3240103

## Technical data

### Dimensions

Inner diameter (f)	13 mm
Material thickness (g)	1.5 mm

### Ambient conditions

Ambient temperature (operation)	110 °C
---------------------------------	--------

### General

Color	silver
Stripping length	14 mm
Material	Copper
Coating	tin-plated

### Standards and Regulations

Design according to standard	DIN 46234
------------------------------	-----------

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 5.1	27400200
eCl@ss 6.0	27400200
eCl@ss 7.0	27400203
eCl@ss 8.0	27400204
eCl@ss 9.0	27400204

### ETIM

ETIM 2.0	EC000005
ETIM 3.0	EC000005
ETIM 4.0	EC001052
ETIM 5.0	EC001052
ETIM 6.0	EC001052
ETIM 7.0	EC001052

### UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	27121703
UNSPSC 11	27121703

# Ring cable lug - C-RC 25/M12 DIN - 3240103

## Classifications

### UNSPSC

UNSPSC 12.01	27121703
UNSPSC 13.2	27121707

## Approvals

### Approvals

---

### Approvals

EAC / EAC

---

### Ex Approvals

---

## Approval details

EAC		7500651.22.01.00246
-----	---	---------------------

EAC		EAC-Zulassung
-----	---	---------------

---