

Connector - C-SCF 1,5/4,8X0,5 - 3240154

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Slip-on sleeve, non-insulated, 0.75 ... 1.5 mm², 4.8 x 0.5

Why buy this product

- The uninsulated slip-on sleeves and flat plugs are made from electrolytically tin-plated brass
- They round out the product range in terms of connectors

Key Commercial Data

Packing unit	1 STK
Minimum order quantity	100 STK
GTIN	 4 046356 453714
GTIN	4046356453714
Weight per Piece (excluding packing)	0.430 g
Custom tariff number	85369010
Country of origin	Germany

Technical data

Dimensions

Length (b)	15.6 mm
Width (a)	4.8 mm
Maximum stripping length	7 mm
Material thickness (g)	0.4 mm

Ambient conditions

Ambient temperature (operation)	110 °C
---------------------------------	--------

Connector - C-SCF 1,5/4,8X0,5 - 3240154

Technical data

General


Color	silver
Stripping length	7 mm
Components	halogen-free
Material	Brass
Insulating material	nicht zutreffend
Coating	tin-plated

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Dimensional drawing



Classifications

eCl@ss

eCl@ss 4.0	27060701
eCl@ss 4.1	27060701
eCl@ss 5.0	27400201
eCl@ss 5.1	27400201
eCl@ss 6.0	27400201
eCl@ss 7.0	27400201
eCl@ss 8.0	27400204
eCl@ss 9.0	27400212

ETIM

ETIM 2.0	EC000005
ETIM 3.0	EC000005
ETIM 4.0	EC001052

Connector - C-SCF 1,5/4,8X0,5 - 3240154

Classifications

ETIM

ETIM 5.0	EC000516
ETIM 6.0	EC001059

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121707

Approvals


Approvals


Approvals

EAC / EAC

Ex Approvals

Approval details

EAC		7500651.22.01.00246
-----	---	---------------------

EAC		EAC-Zulassung
-----	---	---------------

Accessories

Accessories

Crimping tool

Connector - C-SCF 1,5/4,8X0,5 - 3240154

Accessories

Crimping pliers - CRIMPFOX-SC 1,5 - 1212048



Crimping pliers, for non-insulated slip-on sleeves 2.8 and 4.8 mm, 0.1 - 1.5 mm², B crimp

Crimping pliers - CRIMPFOX-SC 1,5-M - 1212725



Crimping pliers, for non-insulated slip-on sleeves 2.8 and 4.8 mm, 0.1 - 1.5 mm², B crimp

Crimping pliers - CRIMPFOX-SC 6 - 1212050



Crimping pliers, for uninsulated slip-on sleeves 2.8, 4.8, and 6.3 mm, 0.5 - 6 mm², B crimp

Die

Replacement die - CF 500/DIE SC 1,5 - 1212241



Die for crimping machine CF 500, for slip-on sleeves and flat connectors (C-SCF... and C-SCM...) 0.1 ... 1.5 mm²

Replacement die - CF 500/DIE SC 6 - 1212242



Die for crimping machine CF 500, for slip-on sleeves and flat connectors (C-SCF... and C-SCM...) 0.5 ... 6 mm²
