

ZBF 8/WH-100:UNBEDRUCKT - Zack Marker strip, flat



0808794

<https://www.phoenixcontact.com/nl/products/0808794>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack Marker strip, flat, Strip, white, unmarked, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 8 mm, Number of individual labels: 1000, text field height: 8.15 mm, text field width: 5.15 mm

Your advantages

- The ZBF zack marker strip system with flat marker groove is a marking solution for modular terminal blocks and electronics modules
- Other pitches available on request
- Unmarked marking strips can be custom-labeled with a plotter or by hand
- The multi-section marking strips are easy to fit and can be easily separated if required

Commercial data

Item number	0808794
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BG2112
Product key	BG2112
GTIN	4017918180331
Weight per piece (including packing)	0,55 g
Weight per piece (excluding packing)	0,55 g
Customs tariff number	39269097
Country of origin	DE

Technical data

Product properties

Pitch	8 mm
-------	------

Marking

Number of individual labels	1000
Number of individual labels per row	10
Number of marker strips	100
Slot type	flat

Dimensions

Width	8.15 mm
Height	6.40 mm
Depth	1.60 mm
Pitch	8 mm

Text field

Text field width	5.15 mm
Text field height	8.15 mm

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Standards and regulations


Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	latching
---------------	----------

Drawings

Schematic diagram



ZBF 8/WH-100:UNBEDRUCKT - Zack Marker strip, flat



0808794

<https://www.phoenixcontact.com/nl/products/0808794>

Classifications

ECLASS

ECLASS-13.0	27281101
-------------	----------

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

0808794

<https://www.phoenixcontact.com/nl/products/0808794>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0,007 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl