

SK 5,0 REEL P10 WH CUS - Marker card



0825129

<https://www.phoenixcontact.com/nl/products/0825129>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marker card, Roll, can be ordered: by card, white, labeled according to customer specifications, mounting type: adhesive, for terminal block width: 10 mm, Number of individual labels: 10



Commercial data

Item number	0825129
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BG8113
Product key	BG8113
GTIN	4046356355100
Weight per piece (including packing)	1,97 g
Weight per piece (excluding packing)	0,6 g
Customs tariff number	49119900
Country of origin	PL

SK 5,0 REEL P10 WH CUS - Marker card



0825129

<https://www.phoenixcontact.com/nl/products/0825129>

Technical data

Notes

Order information:	Marking up to max. 25-pos.
--------------------	----------------------------

Product properties

Pitch	10 mm
-------	-------

Marking

Number of individual labels	10
Number of individual labels per row	1
Number of marker strips	10
Slot type	Label
Identification technology	Thermal transfer

Dimensions

Width	50.00 mm
Height	5.00 mm
Depth	0.10 mm
Pitch	10 mm

Material specifications

Foil strength	53 µm
Adhesive strength	20 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Material	Polyester
Base element material	Polyester
Components	free from silicone and halogen

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

SK 5,0 REEL P10 WH CUS - Marker card



0825129

<https://www.phoenixcontact.com/nl/products/0825129>

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

SK 5,0 REEL P10 WH CUS - Marker card


0825129

<https://www.phoenixcontact.com/nl/products/0825129>



Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

SK 5,0 REEL P10 WH CUS - Marker card



0825129

<https://www.phoenixcontact.com/nl/products/0825129>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

SK 5,0 REEL P10 WH CUS - Marker card



0825129

<https://www.phoenixcontact.com/nl/products/0825129>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl