

ZBF 16:UNPRINTED - Zack Marker strip, flat



0827464

<https://www.phoenixcontact.com/nl/products/0827464>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack Marker strip, flat, Strip, white, unmarked, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 16 mm, Number of individual labels: 50, text field height: 10.5 mm, text field width: 16.25 mm

Your advantages

- Unmarked marking strips can be custom-labeled with a plotter or by hand
- Other pitches available on request
- The ZBF zack marker strip system with flat marker groove is a marking solution for modular terminal blocks and electronics modules
- The multi-section marking strips are easy to fit and can be easily separated if required

Commercial data

Item number	0827464
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG2112
Product key	BG2112
GTIN	4046356431439
Weight per piece (including packing)	0,71 g
Weight per piece (excluding packing)	0,7 g
Customs tariff number	39269097
Country of origin	DE

ZBF 16:UNPRINTED - Zack Marker strip, flat



0827464

<https://www.phoenixcontact.com/nl/products/0827464>

Technical data

Notes

General	Can be labeled with CMS
General	Can be labeled with CMS

Product properties

Pitch	16 mm
-------	-------

Marking

Number of individual labels	50
Number of individual labels per row	5
Number of marker strips	10
Slot type	flat

Dimensions

Width	16.00 mm
Height	6.40 mm
Depth	1.60 mm
Pitch	16 mm

Text field

Text field width	16.25 mm
Text field height	10.5 mm

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

Environmental and real-life conditions

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	latching
---------------	----------

ZBF 16:UNPRINTED - Zack Marker strip, flat

0827464

<https://www.phoenixcontact.com/nl/products/0827464>



Drawings

Schematic diagram



ZBF 16:UNPRINTED - Zack Marker strip, flat



0827464

<https://www.phoenixcontact.com/nl/products/0827464>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

ZBF 16:UNPRINTED - Zack Marker strip, flat



0827464

<https://www.phoenixcontact.com/nl/products/0827464>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0,007 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl