

ZBF 12 CUS - Zack Marker strip, flat



0825018

<https://www.phoenixcontact.com/nl/products/0825018>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack Marker strip, flat, can be ordered: Strip, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 12 mm, Number of individual labels: 5, text field height: 12.15 mm, text field width: 5.15 mm

Your advantages

- The ZBF zack marker strip system with flat marker groove is a marking solution for modular terminal blocks and electronics modules
- Other pitches available on request
- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- The multi-section marking strips are easy to fit and can be easily separated if required

Commercial data

Item number	0825018
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BG8112
Product key	BG8112
GTIN	4046356357555
Weight per piece (including packing)	0,603 g
Weight per piece (excluding packing)	0,57 g
Customs tariff number	49119900
Country of origin	PL

ZBF 12 CUS - Zack Marker strip, flat



0825018

<https://www.phoenixcontact.com/nl/products/0825018>

Technical data

Product properties

Pitch	12 mm
-------	-------

Marking

Number of individual labels	5
Number of individual labels per row	5
Number of marker strips	1
Slot type	flat

Dimensions

Width	12.15 mm
Height	6.40 mm
Depth	1.60 mm
Pitch	12 mm

Text field

Text field width	5.15 mm
Text field height	12.15 mm

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

Environmental and real-life conditions

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	snap into flat marker groove
---------------	------------------------------

ZBF 12 CUS - Zack Marker strip, flat


0825018

<https://www.phoenixcontact.com/nl/products/0825018>



Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

ZBF 12 CUS - Zack Marker strip, flat



0825018

<https://www.phoenixcontact.com/nl/products/0825018>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

ZBF 12 CUS - Zack Marker strip, flat



0825018

<https://www.phoenixcontact.com/nl/products/0825018>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl