

HC-B 24-TMS-EEE-PR-DI - Profile gasket



1409820

<https://www.phoenixcontact.com/nl/products/1409820>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Profile gasket for sleeve housing type B24.....EEE



Commercial data

Item number	1409820
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AF7APZ
Product key	AF7APZ
GTIN	4046356750899
Weight per piece (including packing)	6,85 g
Weight per piece (excluding packing)	5,97 g
Customs tariff number	40169300
Country of origin	DE

HC-B 24-TMS-EEE-PR-DI - Profile gasket

1409820

<https://www.phoenixcontact.com/nl/products/1409820>




Technical data

Product properties

Type	B24
------	-----

Dimensions

Dimensional drawing	
Width	55 mm
Height	7.8 mm
Length	149.5 mm

Material specifications

Material	NBR, conductive
----------	-----------------

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 125 °C

HC-B 24-TMS-EEE-PR-DI - Profile gasket




1409820

<https://www.phoenixcontact.com/nl/products/1409820>

Drawings

Dimensional drawing



Dimensional drawing

HC-B 24-TMS-EEE-PR-DI - Profile gasket



1409820

<https://www.phoenixcontact.com/nl/products/1409820>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/1409820>



EAC

Approval ID: RU C-DE.AI30.B.01102

HC-B 24-TMS-EEE-PR-DI - Profile gasket



1409820

<https://www.phoenixcontact.com/nl/products/1409820>

Classifications

ECLASS

ECLASS-13.0	23071590
ECLASS-15.0	27440292

ETIM

ETIM 10.0	EC011638
-----------	----------

UNSPSC

UNSPSC 21.0	31401600
-------------	----------

HC-B 24-TMS-EEE-PR-DI - Profile gasket



1409820

<https://www.phoenixcontact.com/nl/products/1409820>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl