

A-INL-M63-P-BK - Counter nut



1411220

<https://www.phoenixcontact.com/nl/products/1411220>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Counter nut, for threads M63 x 1.5, color: jet black



Commercial data

Item number	1411220
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	AF7DZX
Product key	AF7DZX
GTIN	4046356923521
Weight per piece (including packing)	17,57 g
Weight per piece (excluding packing)	17 g
Customs tariff number	39269097
Country of origin	TR

A-INL-M63-P-BK - Counter nut

1411220

<https://www.phoenixcontact.com/nl/products/1411220>




Technical data

Product properties

Thread type	M63
-------------	-----

Dimensions

Dimensional drawing		
Length	8 mm	
Diameter	63 mm	
Connecting thread diameter	63 mm	
Wrench size, counter nut	75 mm	
Hexagon angular dimension	82.5 mm	
Thread type connection side	M63 x 1.5	
Thread pitch	1.5 mm	

Material specifications

Material	PA
Flammability rating according to UL 94	V2

Cable/line

Halogen-free	yes
--------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

A-INL-M63-P-BK - Counter nut


1411220

<https://www.phoenixcontact.com/nl/products/1411220>



Drawings

Dimensional drawing



A-INL-M63-P-BK - Counter nut



1411220

<https://www.phoenixcontact.com/nl/products/1411220>

Classifications

ECLASS

ECLASS-13.0	27140807
ECLASS-15.0	27140807

ETIM

ETIM 10.0	EC003608
-----------	----------

UNSPSC

UNSPSC 21.0	31161700
-------------	----------

A-INL-M63-P-BK - Counter nut



1411220

<https://www.phoenixcontact.com/nl/products/1411220>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl