

A-INL-PG42-P-GY - Counter nut



1411229

<https://www.phoenixcontact.com/nl/products/1411229>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Counter nut, for threads Pg42, color: silver-gray RAL 7001



Commercial data

Item number	1411229
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	AF7DZX
Product key	AF7DZX
GTIN	4046356923613
Weight per piece (including packing)	13,8 g
Weight per piece (excluding packing)	13,8 g
Customs tariff number	39269097
Country of origin	TR

A-INL-PG42-P-GY - Counter nut

1411229

<https://www.phoenixcontact.com/nl/products/1411229>




Technical data

Product properties

Thread type	Pg42
-------------	------

Dimensions

Dimensional drawing	
Length	8 mm
Diameter	54 mm
Connecting thread diameter	54 mm
Wrench size, counter nut	65 mm
Hexagon angular dimension	73 mm
Thread type connection side	Pg42

Material specifications

Material	PA
Flammability rating according to UL 94	V2

Cable/line

Halogen-free	yes
--------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

A-INL-PG42-P-GY - Counter nut


1411229

<https://www.phoenixcontact.com/nl/products/1411229>



Drawings

Dimensional drawing



A-INL-PG42-P-GY - Counter nut



1411229

<https://www.phoenixcontact.com/nl/products/1411229>

Classifications

ECLASS

ECLASS-13.0	27140807
ECLASS-15.0	27140807

ETIM

ETIM 10.0	EC003608
-----------	----------

UNSPSC

UNSPSC 21.0	31161700
-------------	----------

A-INL-PG42-P-GY - Counter nut



1411229

<https://www.phoenixcontact.com/nl/products/1411229>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl