


EB 10- 8 - Insertion bridge

0202138

<https://www.phoenixcontact.com/in/products/0202138>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

Insertion bridge, pitch: 8 mm, number of positions: 10, color: gray



Commercial Data

Item number	0202138
Packing unit	10 pc
Minimum order quantity	10 pc
Sales Key	BE1
Product Key	BE1Z2X
Catalog Page	Page 117 (C-1-2019)
GTIN	4017918098261
Weight per Piece (including packing)	12.06 g
Weight per Piece (excluding packing)	11.524 g
Customs tariff number	85366990
Country of origin	CN

EB 10- 8 - Insertion bridge



0202138

<https://www.phoenixcontact.com/in/products/0202138>

Technical Data

Product properties

Product type	Insertion bridge
Number of positions	10
Pitch	8 mm

Dimensions

Pitch	8 mm
-------	------

Material specifications

Color	gray
Material	Copper
Insulating material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	Screw mounting
---------------	----------------

EB 10- 8 - Insertion bridge



0202138

<https://www.phoenixcontact.com/in/products/0202138>

Classifications

ECLASS

ECLASS-10.0.1	27141140
ECLASS-11.0	27141140
ECLASS-12.0	27141140
ECLASS-13.0	27250303

ETIM

ETIM 8.0	EC000489
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

EB 10- 8 - Insertion bridge



0202138

<https://www.phoenixcontact.com/in/products/0202138>

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in