

A-INSP-PG16-65N-P-BK - Screw plug



1415213

<https://www.phoenixcontact.com/nl/products/1415213>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Screw plug, material for screw connection: PA, connecting thread: Pg16, color: jet black RAL 9005, with O-ring



Commercial data

Item number	1415213
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AF7DZX
Product key	AF7DZX
GTIN	4055626038568
Weight per piece (including packing)	2,2 g
Weight per piece (excluding packing)	2,17 g
Customs tariff number	39269097
Country of origin	DE

A-INSP-PG16-65N-P-BK - Screw plug




1415213

<https://www.phoenixcontact.com/nl/products/1415213>

Technical data

Dimensions

Dimensional drawing	
Length	9.5 mm
Length of the connecting thread	6 mm
Diameter	22.5 mm
	27 mm
	27 mm
Connecting thread diameter	22.5 mm
Hexagon angular dimension	Diameter
Thread type connection side	Pg16

Material specifications


Material	PA
Seal material Flat gasket	EPDM
Material for screw connection	PA

Environmental and real-life conditions


Ambient conditions	
Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 100 °C

Drawings

Dimensional drawing



Dimensional drawing



A-INSP-PG16-65N-P-BK - Screw plug



1415213

<https://www.phoenixcontact.com/nl/products/1415213>

Classifications

ECLASS

ECLASS-13.0	23111190
ECLASS-15.0	27140805

ETIM

ETIM 10.0	EC002374
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

A-INSP-PG16-65N-P-BK - Screw plug



1415213

<https://www.phoenixcontact.com/nl/products/1415213>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl