

A-INL-M16-P-LG - Counter nut

1417660

<https://www.phoenixcontact.com/nl/products/1417660>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Counter nut, for threads M16 x 1.5, color: light gray



Commercial data

Item number	1417660
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AF7DZX
Product key	AF7DZX
GTIN	4055626121635
Weight per piece (including packing)	1,77 g
Weight per piece (excluding packing)	1,48 g
Customs tariff number	39269097
Country of origin	TR

A-INL-M16-P-LG - Counter nut

1417660


<https://www.phoenixcontact.com/nl/products/1417660>

Technical data

Product properties

Thread type	M16
-------------	-----

Dimensions

Dimensional drawing	
Length	5 mm
Diameter	16 mm
Connecting thread diameter	16 mm
Wrench size, counter nut	22 mm
Hexagon angular dimension	24.2 mm
Thread type connection side	M16 x 1.5
Thread pitch	1.5 mm

Material specifications

Material	PA 6.6 GF
----------	-----------

Cable/line

Halogen-free	yes
--------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

A-INL-M16-P-LG - Counter nut


1417660

<https://www.phoenixcontact.com/nl/products/1417660>



Drawings

Dimensional drawing



A-INL-M16-P-LG - Counter nut



1417660

<https://www.phoenixcontact.com/nl/products/1417660>

Classifications

ECLASS

ECLASS-13.0	27140807
ECLASS-15.0	27140807

ETIM

ETIM 10.0	EC003608
-----------	----------

UNSPSC

UNSPSC 21.0	31161700
-------------	----------

A-INL-M16-P-LG - Counter nut



1417660

<https://www.phoenixcontact.com/nl/products/1417660>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl