

FBP-3/3 TR - Cover profile

3069927

<https://www.phoenixcontact.com/nl/products/3069927>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cover profile, depth: 32 mm, width: 74.1 mm, height: 57.1 mm, color: transparent



Commercial data

Item number	3069927
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE6113
Product key	BE6113
GTIN	4055626299914
Weight per piece (including packing)	59,5 g
Weight per piece (excluding packing)	59,5 g
Customs tariff number	85366990
Country of origin	PL

Technical data

Product properties

Product family	FAME 3
----------------	--------

Insulation characteristics

Overvoltage category	III
----------------------	-----

Dimensions

Width	74.1 mm
Height	57.1 mm
Depth	32 mm

Material specifications

Color	transparent
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PVC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

FBP-3/3 TR - Cover profile

3069927

<https://www.phoenixcontact.com/nl/products/3069927>



Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27141190

ETIM

ETIM 10.0	EC002848
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FBP-3/3 TR - Cover profile

3069927

<https://www.phoenixcontact.com/nl/products/3069927>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl