

WP-STEEL PVC C 10 - Protective hose



3240867

<https://www.phoenixcontact.com/nl/products/3240867>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective hose, material: Steel, galvanized / PVC, degree of protection: IP68, color: black, inside diameter: 7 mm, Total length: 10 m

Commercial data

Item number	3240867
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AF7DSA
Product key	AF7DSA
GTIN	4046356737227
Weight per piece (including packing)	999,9 g
Weight per piece (excluding packing)	999,9 g
Customs tariff number	83071000
Country of origin	DE

WP-STEEL PVC C 10 - Protective hose



3240867

<https://www.phoenixcontact.com/nl/products/3240867>

Technical data

Notes

Notes on operation	Protective hose length is measured stretched out; length tolerance $\pm 5\%$
--------------------	--

Product properties

Tensile strength GRP	500 N
----------------------	-------

Dimensions

Internal dimensions

Internal diameter	7 mm
-------------------	------

Material specifications

Material	Steel, galvanized / PVC
----------	-------------------------

Cable/line

Bending radius, dynamic	65 mm
Bending radius, static	25 mm
Tensile strength	500 N
Halogen-free	no

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP68
Ambient temperature (operation)	-25 °C ... 90 °C
Short-term temperature	100 °C

WP-STEEL PVC C 10 - Protective hose



3240867

<https://www.phoenixcontact.com/nl/products/3240867>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/3240867>



VDE approval of drawings

WP-STEEL PVC C 10 - Protective hose



3240867

<https://www.phoenixcontact.com/nl/products/3240867>

Classifications

ECLASS

ECLASS-13.0	27430301
ECLASS-15.0	27430301

ETIM

ETIM 10.0	EC001179
-----------	----------

UNSPSC

UNSPSC 21.0	40141700
-------------	----------

WP-STEEL PVC C 10 - Protective hose



3240867

<https://www.phoenixcontact.com/nl/products/3240867>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl