

WP-FS IP68 M10 - Flat gasket

3241159

<https://www.phoenixcontact.com/nl/products/3241159>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Flat gasket, material: Perbunan, degree of protection: IP68, color: black, inside diameter: 10 mm



Your advantages

- The Perbunan flat sealing rings are used to seal protective hose screw connections on uneven surfaces.
- Up to IP68 protection is achieved.

Commercial data

Item number	3241159
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AF7DSA
Product key	AF7DSA
GTIN	4046356785655
Weight per piece (including packing)	0,38 g
Weight per piece (excluding packing)	0,37 g
Customs tariff number	40169300
Country of origin	DE

WP-FS IP68 M10 - Flat gasket

3241159

<https://www.phoenixcontact.com/nl/products/3241159>



Technical data

Product properties

Thread type	M10
-------------	-----

Dimensions

Height	1.6 mm
Diameter	17 mm
Panel thickness	1.6 mm

Internal dimensions

Internal diameter	10 mm
-------------------	-------

Material specifications

Material	Perbunan
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP68
Ambient temperature (operation)	-20 °C ... 120 °C

WP-FS IP68 M10 - Flat gasket



3241159

<https://www.phoenixcontact.com/nl/products/3241159>

Classifications

ECLASS

ECLASS-13.0	27430319
ECLASS-15.0	27430319

ETIM

ETIM 10.0	EC001181
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

WP-FS IP68 M10 - Flat gasket

3241159

<https://www.phoenixcontact.com/nl/products/3241159>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl