

EB 4-25/PT - Insertion bridge




3260161

<https://www.phoenixcontact.com/nl/products/3260161>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insertion bridge, pitch: 25 mm, number of positions: 4, nominal current: 150 A, length: 73 mm, color: red



Commercial data

Item number	3260161
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE2Z2X
Product key	BE2Z2X
GTIN	4055626137476
Weight per piece (including packing)	109,58 g
Weight per piece (excluding packing)	109,58 g
Customs tariff number	85389099
Country of origin	PL

EB 4-25/PT - Insertion bridge



3260161

<https://www.phoenixcontact.com/nl/products/3260161>

Technical data

Product properties

Number of positions	4
Pitch	25 mm

Electrical properties

Maximum load current	150 A
----------------------	-------

Connection data

Maximum load current	150 A
----------------------	-------

Dimensions

Width	97.8 mm
Height	73.3 mm
Depth	28.6 mm
Length	73.3 mm
Pitch	25 mm

Material specifications

Color	red (RAL 3001)
Material	Metal
Flammability rating according to UL 94	V0
Coating	tin-plated
Insulating material	PA

Mounting

Mounting type	Plug-in mounting
---------------	------------------

EB 4-25/PT - Insertion bridge

3260161

<https://www.phoenixcontact.com/nl/products/3260161>



Classifications

ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

ETIM

ETIM 10.0	EC000489
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

EB 4-25/PT - Insertion bridge



3260161

<https://www.phoenixcontact.com/nl/products/3260161>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl