

SKBI 64/E48 - Plug-in card block



2264080

<https://www.phoenixcontact.com/nl/products/2264080>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



BOX



19" plug-in card block, color: green, number of positions: 48, product range: SKBI 64, pitch: 5.08 mm, type of packaging: packed in cardboard

Commercial data

Item number	2264080
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AARHAD
Product key	AARHAD
GTIN	4017918053901
Weight per piece (including packing)	306,6 g
Weight per piece (excluding packing)	305,8 g
Customs tariff number	85369010
Country of origin	DE

SKBI 64/E48 - Plug-in card block

2264080

<https://www.phoenixcontact.com/nl/products/2264080>



Technical data


Product properties

Product family	SKBI 64
Type	IEC 60603-2/DIN 41612 - E
Number of positions	48
Pitch	5.08 mm

Connection data

Connection method	Screw connection with tension sleeve
Stripping length	8 mm
Screw thread	M3

Dimensions

Dimensional drawing	
Width	118 mm
Height	162 mm
Length	66 mm
Hole diameter	4.2 mm
Pitch	5.08 mm

Material specifications

Color (Housing)	green (RAL 6021)
-----------------	------------------

Standards and regulations

Connection in acc. with standard	EN-VDE
----------------------------------	--------

Packaging specifications

Type of packaging	packed in cardboard
-------------------	---------------------

SKBI 64/E48 - Plug-in card block


2264080

<https://www.phoenixcontact.com/nl/products/2264080>



Drawings

Dimensional drawing




SKBI 64/E48 - Plug-in card block

2264080

<https://www.phoenixcontact.com/nl/products/2264080>



Schematic diagram



SKBI 64/E48 - Plug-in card block



2264080

<https://www.phoenixcontact.com/nl/products/2264080>

Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SKBI 64/E48 - Plug-in card block

2264080

<https://www.phoenixcontact.com/nl/products/2264080>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl