



Extract from the online catalog

ME 12,5 OT-MKDSO SET

Order No.: 2907457

Illustration shows a fully mounted version of the electronic housing



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2907457>

Housing upper part, complete with PCB termination blocks for full equipping. 12-pos., housing width: 12.5 mm

Commercial data	
EAN	4017918131548
Pack	1 pcs.
Customs tariff	85369010
Weight/Piece	0.0241 KG
Catalog page information	Page 574 (CC-2009)

Product notes

WEEE/RoHS-compliant since:
01/01/2003

<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Certificates / Approvals



Certification

CUL, UL

ME 12,5 OT-MKDSO SET Order No.: 2907457
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2907457>

CUL

Nominal voltage U_N	300 V
Nominal current I_N	10 A
AWG/kcmil	30-12

UL

Nominal voltage U_N	300 V
Nominal current I_N	10 A
AWG/kcmil	30-12

Article Sets

Item	Designation	Description
Allgemein		
2906830	ME 12,5 OT-MKDSO GN	Housing upper part, for printed circuit terminal block connection
1707205	MKDSO 2,5/ 2-L	PC terminal block, Nominal current: 24 A, Nom. voltage: 250 V, Pitch: 5 mm, Number of positions: 2, Type of connection: Screw connection, Assembly: Soldering, Conductor/PCB connection direction: 0 °, Color: green, Article with lateral pin exit
1707195	MKDSO 2,5/ 2-R	PC terminal block, Nominal current: 24 A, Nom. voltage: 320 V, Pitch: 5 mm, Number of positions: 2, Type of connection: Screw connection, Assembly: Soldering, Conductor/PCB connection direction: 0 °, Color: green, Article with lateral pin exit

ME 12,5 OT-MKDSO SET Order No.: 2907457
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2907457>

Address

PHOENIX CONTACT Deutschland GmbH
Flachmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;

onlinecomponents.com