

PIN CODE FLK CABLE

Pin-Code für FLK-Kabel
PIN Code for FLK Cable
Code PIN pour câble FLK



INTERFACE

Datenblatt
Data Sheet
Fiche technique
102197_01_ia

© PHOENIX CONTACT - 04/2007

Aderzahl Number of Wires Nombre de fils	X1	X2	Aderfarbe	Wire Color	Couleur du fil	
10-polig	1	1	schwarz	black	noir	(BK)
10-pos.	2	2	braun	brown	marron	(BN)
10 pôles	3	3	rot	red	rouge	(RD)
	4	4	orange	orange	orange	(OG)
	5	5	gelb	yellow	jaune	(YE)
	6	6	grün	green	vert	(GN)
	7	7	blau	blue	bleu	(BU)
	8	8	violett	violet	violet	(VT)
	9	9	grau	gray	gris	(GY)
	10	10	weiß	white	blanc	(WH)
14-polig	11	11	weiß-schwarz	white-black	blanc-noir	(WH/BK)
14-pos.	12	12	weiß-braun	white-brown	blanc-marron	(WH/BN)
14 pôles	13	13	weiß-rot	white-red	blanc-rouge	(WH/RD)
	14	14	weiß-orange	white-orange	blanc-orange	(WH/OG)
16-polig	15	15	weiß-gelb	white-yellow	blanc-jaune	(WH/YE)
16-pos.	16	16	weiß-grün	white-green	blanc-vert	(WH/GN)
16 pôles						
20-polig	17	17	weiß-blau	white-blue	blanc-bleu	(WH/BU)
20-pos.	18	18	weiß-violett	white-violet	blanc-violet	(WH/VT)
20 pôles	19	19	weiß-grau	white-gray	blanc-gris	(WH/GY)
	20	20	braun-schwarz	brown-black	marron-noir	(BN/BK)
26-polig	21	21	braun-rot	brown-red	marron-rouge	(BN/RD)
26-pos.	22	22	braun-orange	brown-orange	marron-orange	(BN/OG)
26 pôles	23	23	braun-gelb	brown-yellow	marron-jaune	(BN/YE)
	24	24	braun-grün	brown-green	marron-vert	(BN/GN)
	25	25	braun-blau	brown-blue	marron-bleu	(BN/BU)
	26	26	braun-violett	brown-violet	marron-violet	(BN/VT)
34-polig	27	27	braun-grau	brown-gray	marron-gris	(BN/GY)
34-pos.	28	28	braun-weiß	brown-white	marron-blanc	(BN/WH)
34 pôles	29	29	grün-schwarz	green-black	vert-noir	(GN/BK)
	30	30	grün-braun	green-brown	vert-marron	(GN/BN)
	31	31	grün-rot	green-red	vert-rouge	(GN/RD)
	32	32	grün-orange	green-orange	vert-orange	(GN/OG)
	33	33	grün-blau	green-blue	vert-bleu	(GN/BU)
	34	34	grün-violett	green-violet	vert-violet	(GN/VT)
40-polig	35	35	grün-grau	green-gray	vert-gris	(GN/GY)
40-pos.	36	36	grün-weiß	green-white	vert-blanc	(GN/WH)
40 pôles	37	37	gelb-schwarz	yellow-black	jaune-noir	(YE/BK)
	38	38	gelb-braun	yellow-brown	jaune-marron	(YE/BN)
	39	39	gelb-rot	yellow-red	jaune-rouge	(YE/RD)
	40	40	gelb-orange	yellow-orange	jaune-orange	(YE/OG)
50-polig	41	41	gelb-blau	yellow-blue	jaune-bleu	(YE/BU)
50-pos.	42	42	gelb-violett	yellow-violet	jaune-violet	(YE/VT)
50 pôles	43	43	gelb-grau	yellow-gray	jaune-gris	(YE/GY)
	44	44	gelb-weiß	yellow-white	jaune-blanc	(YE/WH)
	45	45	grau-schwarz	gray-black	gris-noir	(GY/BK)
	46	46	grau-braun	gray-brown	gris-marron	(GY/BN)
	47	47	grau-rot	gray-red	gris-rouge	(GY/RD)
	48	48	grau-orange	gray-orange	gris-orange	(GY/OG)
	49	49	grau-gelb	gray-yellow	gris-jaune	(GY/YE)
	50	50	grau-grün	gray-green	gris-vert	(GY/GN)

PHOENIX CONTACT GmbH & Co. KG • 32823 Blomberg • Germany
Phone: +49-(0) 5235-3-00 • Fax: +49-(0) 5235-3-4 12 00
www.phoenixcontact.com