


Search Results

- Evaluate
 - FAQ's
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'F6LE3-10FM3'

Your search criteria matched only one product, shown below

F6LE3-10FM3




- Pass all TIA/EIA-568-B.3 performance requirements
- Insertion loss per connection: 0.10dB typical; 0.30dB maximum
- Include color-specific keys with positive and negative keying features to visually and mechanically distinguish connections to prevent unauthorized mating with unlike keyed or non-keyed adapters
- Part of a complete keyed LC system that includes *Opti-Core*® Patch Cords and Pigtails, *OptiCam*® Pre-Polished Cam Connectors, *Opticom*® Fiber Adapter Panels (FAPs) and *Mini-Com*® Adapter Modules
- Factory terminated and 100% tested for insertion loss
- Insertion loss data recorded for every multimode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- Highest quality flame retardant fiber optic cable with tight -buffered coating on each optical fiber

Additional lengths and availability: Keyed LC patch cords and pigtails are available in 1m – 10m lengths in 1m increments, and 15m, 20m, and 30m lengths. For other lengths, contact

Customer Service for actual lead times.

Additional keyed colors include the following: G– Violet, H– Aqua, J– Rose, K– Slate, L– Brown, P– White, Q– Charcoal, R– Lavender, S– Peach, T– Steel Blue, V– Maroon and W– Mint.

Part Number	F6LE3-10FM3
RoHS Compliancy Status	Compliant
Note	Intended for use in fixed installations which are outside the scope of RoHS.
Part Description	SC to keyed LC (keyed F- blue) multimode, low smoke zero halogen, duplex patch cord, 1.6mm jacketed cable (one duplex SC connector on one end and one duplex (keyed F blue) LC connector on the other end) – 62.5/125µm.
Product Type	Keyed LC Patch Cords
Length (m)	3
Fiber Compatibility	62.5/125µm
Fiber Cable Size	1.6mm
Fiber Cable Type	Jacketed
Fiber Type	Multimode 62.5/125
Connector 1 Type	SC Connector
Connector 2 Type	LC Connector- Keyed F (Blue)
Flammability Rating	Low Smoke Zero Haloagen (LSZH)
Key Type and Color	Keyed F (Blue)
Pricing Description	SC to LC (keyed F- blue) 62.5µm Duplex, LSZH, Patch Cord&M
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.