

## Search Results

## Evaluate

- FAQs

## How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

## Home &gt; Product On-Line Catalog &gt; Search Results &gt;

Current refinements (click  to remove) Search Tips Text Search: 'FC12SCSP5Y'

Your search criteria matched only one product, shown below

## FC12SCSP5Y



- Compatible with *Opticom*® and *Opticom*® HD Endosures, Trays, Drawers and Patch Panels
  - Low insertion loss of 1.0dB typical; 1.5dB max. per cassette; ensures system meets IEEE 802.3ae max. channel loss specification of <2.6dB
  - Significantly reduce installation time and labor by eliminating field connector terminations
  - Factory terminated, assembled and 100% tested
  - Insertion loss and return loss data provided on every fiber cassette
  - Lifetime traceability of test data to a Q.C. number on each fiber cassette
- \*MTP is a registered trademark of US Conec Ltd.

**QuickNet™ MTP\* Cassettes cannot be used in an angled patch panel**

|   |   |
|---|---|
| <input type="checkbox"/> Part Number                  | FC12SCSP5Y  |
| <input type="checkbox"/> RoHS Compliancy Status       | Compliant   |
| <input type="checkbox"/> Note                         | FC12SCSP5Y replaces FC12SCSP5   |
| <input type="checkbox"/> Part Description             | OS1/OS2 six singlemode SC duplex adapters to 5 meter pigtail; 12-fiber pre-terminated pigtail cassette. |
| <input type="checkbox"/> Product Type                 | Pre-Terminated Cassettes  |
| <input type="checkbox"/> Fiber Compatibility          | 50/125µm  |
| <input type="checkbox"/> Fiber Type                   | Single  |
| <input type="checkbox"/> CE Compliant                 | No  |
| <input type="checkbox"/> Connection Type              | SC  |
| <input type="checkbox"/> Connector 1 Type             | SC  |
| <input type="checkbox"/> Connector 2 Type             | Pigtail   |
| <input type="checkbox"/> No. of Fibers                | 12  |
| <input type="checkbox"/> Pigtail or MPO               | Pigtail   |
| <input type="checkbox"/> Pricing Description          | 12-Fiber Cassette w/6 Dupl S Connectors Singlemode w/12 SC Pigtail                                      |
| <input type="checkbox"/> Mn. Order UOM                | PC  |
| <input type="checkbox"/> Mn. Order Qty.               | 1   |
| <input type="checkbox"/> BOM Qty. (# of Pkgs.)        | <input type="text" value="0"/>  |
| <input type="checkbox"/> Add to Favorite Product List | <input type="checkbox"/>  |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.