

Search Results

- Evaluate
  - FAQ's
- Design a Solution
  - Catalog Cut Sheet
  - PDFLCDX8-10AF-L
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

Text Search: 'LCDX750-12EF-3'

Your search criteria matched only one product, shown below

**LCDX750-12EF-3**



For Use with Flexible, Extra-Flexible, and Code Stranded Copper Conductors

- Can be used with code conductor and flex conductor class: G, H, I, K, M and Diesel Locomotive
- Generously beveled wire entry prevents bent back strands when inserting conductor into barrel
- Color-coded barrels marked with Panduit and specified competitor die index numbers for proper crimp die selection
- Inspection window to visually assure full conductor insertion
- Tin-plated to inhibit corrosion
- UL Listed and CSA Certified to 35 KV\*\* and temperature rated to 90°C when crimped with Panduit and specified competitor crimping tools and dies
- American Bureau of Shipping Approved
- Available with NEMA hole sizes and spacing

Note: These flex conductor lugs are manufactured for use with AWG wire only.

Part Number	LCDX750-12EF-3
RoHS Compliancy Status	Compliant
Part Description	Flex Lug, 750 kcmil, 2hole, 1/2" Stud Holes, 1.25 Hole Spacing, 90° Angle Tongue
Material	Tin-Plated Copper
Length (In.)	4.20
Length (mm)	106.7
Diesel Locomotive	777.7 kcmil
Stud Hole Size (In.)	1/2
Stud Hole Spacing (In.)	1.25
Tongue Width (In.)	2.17
Barrel Length (In.)	1.66
Angle	90°
Barrel Length (mm)	42.2
CE Compliant	No
Panduit Color Code	Yellow
Panduit Die Index No.	P115
Pricing Description	Copper Compression Lug, 2 Hole, 777.7 kcmil Flex, 1/2" (12.7mm) Stud, 90° Bent
Stud Hole Size (mm)	12.7
Tongue Thickness	0.32
Tongue Type	Standard
Tongue Width (mm)	55.1
Wire Strip Length (In.)	1 3/4
Wire Strip Length (mm)	45.0
Min. Order UOM	PC
Min. Order Qty.	1
Burndy Die Index No.	L115
T&B Die Index No.	115H
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	<input type="button" value="e"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.