

**Search Results**

- Evaluate
  - FAQ's
- Design a Solution
  - Part Drawings
  - PDF-TX5e Shielded ..
  - Specification Sheets
  - PDF-TX5e Keyed S ..
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) Search Tips 

Text Search: 'STPKCH10GR'

Your search criteria matched only one product, shown below

**STPKCH10GR**



- Include all of the same features as the TX5e™ Shielded Patch Cords with the added benefit of visual and mechanical security
- Mechanical keyed configurations prevent unintentional insertion into adjacent ports (6 versions)
- Color-coded for easy identification
- Exceed ANSI/TIA-568-C.2 Category 5e and ISO11801 Class D standards
- Meet requirements of IEEE 802.3af and IEEE 802.3at for PoE applications
- Each patch cord is 100% performance tested and wired T568A
- Constructed of Category 5e, 26 AWG, STP stranded cable and Pan-Plug® Modular Plugs; plug contacts plated with 50 microinches of gold for superior performance
- Plug meets all applicable ANSI/TIA-968-A requirements and exceeds IEC 60603-7 specifications
- Patented tangle free latch prevents snags and provides easy release, saving time on frequent moves, adds, and changes
- Labels on patch cords provide identification of performance level, length, and quality control number
- Optional Patch Cord Color Bands snap on and off individual patch cables offering endless color-coding options
- Optional RJ45 Plug Lock-In Device blocks unauthorized removal of cable, IP phone, other networking equipment or critical connection

▪ Part Number	STPKCH10GR
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Keyed, Category 5e, shielded patch cord with Pan-Plug™ Keyed Shielded Modular Plug on one end and Pan-Plug™ Non-Keyed Shielded Modular Plug on the other end.
▪ Product Type	Keyed Copper Patch Cord
▪ Color	Green
▪ Length (ft.)	10
▪ Length (m)	3.05
▪ Boot Color	Green
▪ Cable Color	International Gray
▪ Cable Type	Shielded
▪ CE Compliant	No
▪ Connector 1 Type	RJ45 8(8)
▪ Connector 2 Type	RJ45 8(8)
▪ Flammability Rating	LSZH/CM
▪ Performance Level	Category 5e/Class D
▪ Pricing Description	Keyed Copper Patch Cord, Cat 5e, Intl Gray STP Cable, 10 Feet
▪ Termination End 1	Keyed Modular Plug
▪ Termination End 2	Non-Keyed Modular Plug
▪ Wiring Scheme	T568B
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.