

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDF-TX6A 10Gig S ..
 - PDF-TX6 PLUS UTP ..
 - Specification Sheets
 - PDF-TX6A 10Gig K ..
 - PDF-TX6 PLUS Key ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips [?](#)

Text Search: 'UTPKSP5OR'

Your search criteria matched only one product, shown below

UTPKSP5OR



- Include all of the same features as the TX6™ PLUS UTP Patch Cords with the added benefit of visual and mechanical security
- Mechanical keyed configurations prevent unintentional insertion into adjacent ports (6 versions)
- Color-coded for easy identification
- Exceed ANSI/TIA-568-C.2 Category 6 and ISO 11801 Class E standards
- Meet requirements of IEEE 802.3af and IEEE 802.3at for PoE applications
- Each patch cord is 100% performance tested and wired T568B
- Constructed of Category 6, 24 AWG UTP stranded cable and TX6™ PLUS Modular Plugs; plug contacts plated with 50 microinches of gold for superior performance
- Plug meets all applicable ANSI/TIA-968-A requirements and exceeds IEC 60603-7 specifications
- Slender strain relief boot provides easy access in high density applications
- Plug uses an integral pair manager to optimize performance and consistency by reducing untwisting of conductors within the plug
- Perform in center of TIA/EIA component range, ensuring interoperability and excellent performance
- Labels on patch cords provide identification of performance level, length, and quality control number
- Patented tangle free latch prevents snags and provides easy release, saving time on frequent moves, adds, and changes
- Optional Patch Cord Color Bands snap on and off individual patch cables offering endless color-coding options
- Optional RJ45 Plug Lock-In Device blocks unauthorized removal of cable, IP phone, other networking equipment or critical connection

| | |
|--------------------------------|---|
| ▪ Part Number | UTPKSP5OR |
| ▪ RoHS Compliancy Status | Compliant |
| ▪ Part Description | Keyed, Category 6, UTP patch cord with TX6™ PLUS Keyed Modular Plug on one end and TX6™ PLUS Non-Keyed Modular Plug on the other end. |
| ▪ Product Type | Keyed Copper Patch Cord |
| ▪ Color | Orange |
| ▪ Length (ft.) | 5 |
| ▪ Length (m) | 1.52 |
| ▪ Cable Color | Orange |
| ▪ Cable Type | UTP |
| ▪ CE Compliant | No |
| ▪ Connector 1 Type | RJ45 8(8) |
| ▪ Connector 2 Type | RJ45 8(8) |
| ▪ Flammability Rating | CM |
| ▪ Performance Level | Category 6/Class E |
| ▪ Pricing Description | Keyed Copper Patch Cord, Cat 6, Orange UTP Cable, 5 Feet |
| ▪ Termination End 1 | Keyed Modular Plug |
| ▪ Termination End 2 | Non-Keyed Modular Plug |
| ▪ Wiring Scheme | T568B |
| ▪ Min. Order UOM | PC |
| ▪ Min. Order Qty. | 1 |
| ▪ BOM Qty. (# of Pkgs.) | <input type="text" value="0"/> |
| ▪ Add to Favorite Product List | <input type="checkbox"/> |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.