

Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) [Search Tips](#) 

 **Text Search: 'UTPKSP10MBL'**

Your search criteria matched only one product, shown below

UTPKSP10MBL



- Include all of the same features as the TX6™ PLUS UTP Patch Cords with the added benefit of visual and mechanical security
- Mechanical keyed configurations prevent unintentional insertion into adjacent ports (6 versions)
- Color-coded for easy identification
- Exceed ANSI/TIA-568-C.2 Category 6 and ISO 11801 Class E standards
- Meet requirements of IEEE 802.3af and IEEE 802.3at for PoE applications
- Each patch cord is 100% performance tested and wired T568B
- Constructed of Category 6, 24 AWG UTP stranded cable and TX6™ PLUS Modular Plugs; plug contacts plated with 50 microinches of gold for superior performance
- Plug meets all applicable ANSI/TIA-968-A requirements and exceeds IEC 60603-7 specifications
- Slender strain relief boot provides easy access in high density applications
- Plug uses an integral pair manager to optimize performance and consistency by reducing

untwisting of conductors within the plug

- Perform in center of TIA/EIA component range, ensuring interoperability and excellent performance
- Labels on patch cords provide identification of performance level, length, and quality control number
- Patented tangle free latch prevents snags and provides easy release, saving time on frequent moves, adds, and changes
- Optional Patch Cord Color Bands snap on and off individual patch cables offering endless color-coding options
- Optional RJ45 Plug Lock-In Device blocks unauthorized removal of cable, IP phone, other networking equipment or critical connection

• Part Number	UTPKSP10MBL
• RoHS Compliancy Status	Compliant
• Part Description	Keyed, Category 6, UTP patch cord with TX6™ PLUS Keyed Modular Plug on one end and TX6™ PLUS Non-Keyed Modular Plug on the other end.
• Product Type	Keyed Copper Patch Cord
• Color	Black
• Length (ft.)	32.81
• Length (m)	10
• Cable Color	Black
• Cable Type	UTP
• Connector 1 Type	RJ45 8(8)
• Connector 2 Type	RJ45 8(8)
• Performance Level	Category 6/Class E
• Pricing Description	Keyed Copper Patch Cord, Cat 6, Black UTP Cable, 10 Meter
• Termination End 1	Keyed Modular Plug
• Min. Order UOM	PC
• Min. Order Qty.	1
• BOM Qty. (# of Pkgs.)	0
• Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.