

**Search Results**

- Evaluate
  - FAQ's
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) Search Tips [?](#)

Text Search: 'UTPSP14GRY-Q'

Your search criteria matched only one product, shown below

**UTPSP14GRY-Q**



- Exceed ANSI/TIA-568-C.2 Category 6 and ISO 11801 Class E standards
- Meet requirements of IEEE 802.3af and IEEE 802.3at for PoE applications
- Each patch cord is 100% performance tested and wired T568B
- Constructed of Category 6, 24 AWG UTP stranded cable and TX6™ PLUS Modular Plugs; plug contacts plated with 50 microinches of gold for superior performance
- Plug meets all applicable ANSI/TIA/EIA-968-A requirements and exceeds IEC 60603-7 specifications
- Slender strain relief boot provides easy access in high density applications
- Plug uses an integral pair manager to optimize performance and consistency by reducing untwisting of conductors within the plug
- Perform in center of TIA/EIA component range, ensuring interoperability and excellent performance
- Labels on patch cords provide identification of performance level, length, and quality control number
- Patented tangle-free latch prevents snags and provides easy release, saving time on frequent moves, adds, and changes
- Optional patch cord color bands snap on and off individual patch cables offering endless color-coding options
- Optional RJ45 plug lock-in device blocks unauthorized removal of cable, IP phone, other networking equipment, or critical connection
- Third party tested for Category 6 component compliance

|                                |  |
|--------------------------------|--|
| ▪ Part Number                  | UTPSP14GRY-Q   |
| ▪ RoHS Compliancy Status       | Compliant  |
| ▪ Part Description             | Category 6, UTP patch cord with TX6™ PLUS Modular Plugs on each end. |
| ▪ Product Type                 | UTP Patch Cord   |
| ▪ Color                        | Green  |
| ▪ Length (ft.)                 | 14   |
| ▪ Length (m)                   | 4.27   |
| ▪ Boot Color                   | Clear  |
| ▪ Cable Type                   | UTP  |
| ▪ CE Compliant                 | No   |
| ▪ Connector 1 Type             | RJ45 8(8)  |
| ▪ Connector 2 Type             | RJ45 8(8)  |
| ▪ Flammability Rating          | CM   |
| ▪ Performance Level            | Category 6   |
| ▪ Pricing Description          | Copper Patch Cord, Cat 6, Green UTP Cable, 14 Feet, Bulk Packaged    |
| ▪ Termination End 1            | Modular Plug   |
| ▪ Termination End 2            | Modular Plug   |
| ▪ Wiring Scheme                | T568B  |
| ▪ Min. Order UOM               | PC   |
| ▪ Min. Order Qty.              | 25   |
| ▪ BOM Qty. (# of Pkgs.)        | <input type="text" value="0"/>                                       |
| ▪ Add to Favorite Product List | <input type="checkbox"/>   |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.