



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'UTPK6A1MGR'

Your search criteria matched only one product, shown below

UTPK6A1MGR



- Include all of the same features as the TX6A™ 10Gig™ UTP Patch Cords with the added benefit of visual and mechanical security
- Mechanical keyed configurations prevent unintentional insertion into adjacent ports (6 versions)
- Color-coded for easy identification
- Exceed ANSI/TIA-568-C.2, ISO 11801 Class E_A Edition 2.1 and IEEE 802.3an-2006 channel requirements for supporting 10GBASE-T
- Meet requirements of IEEE 802.3af and IEEE 802.3at for PoE applications
- Each patch cord is 100% performance tested and wired T568B
- Constructed of TX6A™ 10Gig™ 23 AWG stranded UTP copper cable (nominal cable diameter is .275 inches) and TX6™ PLUS Modular Plugs for superior performance
- Plug meets all applicable ANSI/TIA-968-A requirements and exceeds IEC 60603-7 specifications
- Slender strain relief boot provides easy access in high density applications
- Plug uses an integral pair manager to optimize performance and consistency by reducing untwisting of conductors within the plug
- Plug performance in center of TIA/EIA component range, ensuring interoperability and 10GBASE-T Ethernet channel performance
- Labels on patch cords provide identification of performance level, length, and quality control number
- Patented tangle free latch prevents snags and provides easy release, saving time on frequent moves, adds, and changes
- Optional Patch Cord Color Bands snap on and off individual patch cords offering endless color-coding options

▪ Part Number	UTPK6A1MGR
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Keyed, Category 6A, 10Gb/s UTP patch cord with TX6™ PLUS Keyed Modular Plug on one end and TX6™ PLUS Non-Keyed Modular Plug on the other end.
▪ Product Type	Keyed Copper Patch Cord
▪ Color	Green
▪ Length (ft.)	3.28
▪ Length (m)	1
▪ Cable Color	Green
▪ Cable Type	UTP
▪ Connector 1 Type	RJ45 8(8)
▪ Connector 2 Type	RJ45 8(8)
▪ Performance Level	Category 6A/Class EA
▪ Pricing Description	Keyed Copper Patch Cord, Cat 6A, Green UTP Cable, 1 Meter
▪ Termination End 1	Keyed Modular Plug
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.